



T5 Preheat

F13T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Lamp Current (Nom)	
Base	G5 [G5]		0.170 A
Life To 10% Failures (Nom)	4000 h	Voltage (Nom)	90 V
Life to 50% Failures (Nom)	8000 h	Controls and Dimming	
Life to 50% Failures Preheat (Nom)	8000 h	Dimmable	Yes
System Description	na [-]	Mechanical and Housing	
Light Technical		Bulb Shape	T5 [16 mm (T5)]
Color Code	33-640	Approval and Application	
Initial lumen (Nom)	930 lm	Energy Efficiency Label (EEL)	A
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	4.4 mg
Lumen Maintenance 10000 h (Nom)	58 %	Energy Consumption kWh/1000 h	14 kWh
Lumen Maintenance 2000 h (Nom)	85 %	Product Data	
Lumen Maintenance 5000 h (Nom)	70 %	Order product name	F13T5/CW PH 25PK
Correlated Color Temperature (Nom)	4100 K	EAN/UPC - Product	046677115142
Luminous Efficacy (rated) (Nom)	71 lm/W	Order code	332536
Color Rendering Index (Nom)	60	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power (Rated) (Nom)	13.0 W		

T5 Preheat

Material Nr. (12NC)	928001503332
Net Weight (Piece)	40.200 g
ILCOS Code	FD-13/41/2B-E-G5


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F13T5/CW PH 25PK	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

TL Mini 13W/33-640

Photometric data



LDPB_TL-MINI_33-640-Spectral power distribution B/W



LDPO_TL-MINI_33-640-Spectral power distribution Colour

