



# Switch Start Metal Halide Standard

## MH1000/U/BT37 6PK

High performance, Long life and Superior light qualityA compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information			
Base	E39 [ Single Contact Mogul Screw]	ambient temperatures of 50 degrees F or higher. 1000W types must not be operated at 1500W. (377)	
Operating Position	Universal [ Universal]		
Main Application	General Lighting (G)	Footnotes HID 3	
Life to 50% Failures (Nom)	12000 h	Rated life: Vertical +/- 15 degrees. Other positions 75% of vertical life. (385)	
ANSI Code HID	M47/E	Footnotes HID 4	
Footnotes HID 1	Electrically insulated support for bulb may be required, especially in horizontal and nearly horizontal operating positions. (359)	Vertical lumens. Horizontal lumens 6%–10% lower. (393)	
Footnotes HID 2	Requires a ballast specified or approved for Philips metal halide lamps, or one that is designed to operate all popular brands of metal halide lamps. 1000W types will operate from H36 conventional lag type ballast for Mercury Vapor lamps at	Light Technical	
		Color Code	640 [ CCT of 4000K]
		Luminous Flux (Rated) (Nom)	110000 lm
		Color Designation	Cool White (CW)
		Lumen Maintenance - 40% Life	65 %
		Design Mean Lumens	71500 lm

## Switch Start Metal Halide Standard

Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color Rendering Index (Nom)	65

### Operating and Electrical

Lamp Current (Nom)	4.1 A
Ignition Supply Voltage (Min)	440 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	120 s
Voltage (Nom)	263 V

### Mechanical and Housing

Bulb Finish	Clear
Cap-Base Information	Nic/Brass
Bulb Material	Hard Glass
Bulb Shape	BT37 [ BT37]

### Approval and Application

Energy Saving Product	Not Applicable
-----------------------	----------------

Picogram Per Lumen Hour	176 pg/lm.h
Mercury (Hg) Content (Nom)	151.0 mg

### UV

Pet (Niosh) (Nom)	164 h/500lx
Damage Factor D/fc (Nom)	0.53


### Luminaire Design Requirements

Bulb Temperature (Max)	450 °C
Cap-Base Temperature (Max)	250 °C

### Product Data

Order product name	MH1000/U/BT37 6PK
EAN/UPC - Product	046677321505
Order code	321505
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928601179701
Net Weight (Piece)	0.001 kg

## Dimensional drawing



MH R 1000W/640 E39 BT37 CL U

Product	D	C (max)
MH1000/U/BT37 6PK	4.6 in	11.5 in

