

TECHNICAL DATA

Features

- Measures a wide range of material including; metals, plastic, ceramics, composites, epoxies, glass, and other ultrasonic conductive materials
- Large, easy-to-read backlit LCD display
- User selectable unit of measure (in/mm)
- Internal memory stores up to 500 measurements
- Displays sound velocity at the touch of a button
- Zero adjustment button
- User adjustable High/Low alarms
- Built-in two-point calibration function
- Auto sleep, shut off and low battery indicator
- Includes ultrasonic couplant gel, probe, hard carrying case and batteries

Specifications

Measuring Range:	0.03 to 11.8" (0.65 to 300mm)
Accuracy:	±0.04mm (< 10mm) ±[0.1% rdg.+ 0.04mm] (< 100mm) ±[0.3% rdg.] (> 100mm)
Resolution:	0.01mm or 0.1mm (< 100mm) 0.1mm (>100mm)
Velocity Range:	1000 to 9999 m/s (0.039 to 0.394 in/μs)
Compatible Materials:	Ultrasonic conductive materials (ie. metals, plastics, ceramics, composites, epoxies, glass)
Sampling Time:	Less than 1 sec.
Display:	4-Digit, LCD
Backlit Display:	Yes
Probe Length:	3' (36")
Internal Memory:	Yes (up to 500 readings, 5 files up to 100 each)
Low Battery Indicator:	Yes
Power Supply:	2 AA Batteries
Battery Life:	Approx. 100 hours (Alkaline)
Product Certifications:	CE
Operating Temp.:	32 to 122°F (0 to 50°C)
Storage Temp.:	-4 to 140°F (-20 to 60°C)
Operating Humidity:	20 to 80%
Dimensions:	5.9 x 2.9 x 1.3" (150 x 74 x 32mm)
Weight:	8.4oz (238g)



Model	Description
R7900	Ultrasonic Thickness Gauge
TM-8811PROBE	Replacement Probe
R7950	Ultrasonic Couplant Gel
R7950/12	Ultrasonic Couplant Gel, Pack of 12
CA-52A	Soft Carrying Case
R8888	Deluxe Hard Carrying Case
R7900-NIST	Ultrasonic Thickness Gauge & NIST