# **PHILIPS** Lighting



# Switch Start Metal Halide Standard

## MH400/U/ED28 12PK

High performance, Long life and Superior light qualityA compact, energy efficient metal halide lamp that provides crisp, sparkling light wih long life and high efficiency.

#### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- · Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

#### **Product data**

General Information		Footnotes HID 2	Rated life: Vertical +/- 15 degrees. Other positions
Base	E39 [ Single Contact Mogul Screw]		75% of vertical life. (385)
Operating Position	Universal [ Universal]	Footnotes HID 3	Vertical lumens. Horizontal lumens 6%–10% lower.
Main Application	General Lighting (G)		(393)
Life to 50% Failures (Nom)	20000 h		
ANSI Code HID	M59/E	Light Technical	
Footnotes HID 1	Requires a ballast specified or approved for Philips	Color Code	640 [ CCT of 4000K]
	metal halide lamps, or one that is designed to	Luminous Flux (Rated) (Min)	32000 lm
	operate all popular brands of metal halide lamps.	Luminous Flux (Rated) (Nom)	36000 lm
	1000W types will operate from H36 conventional	Color Designation	Cool White (CW)
	lag type ballast for Mercury Vapor lamps at	Design Mean Lumens	24000 lm
	ambient temperatures of 50 degrees F or higher.	Chromaticity Coordinate X (Nom)	0.390
	1000W types must not be operated at 1500W.	Chromaticity Coordinate Y (Nom)	0.400
	(377)	Correlated Color Temperature (Nom) 4000 K	

### Switch Start Metal Halide Standard

Luminous Efficacy (Rated) (Min)	80 lm/W
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Rendering Index (Nom)	57

#### **Operating and Electrical**


Power (Rated) (Nom)	400 W
Lamp Current (Nom)	3.25 A
Ignition Supply Voltage (Min)	350 V
Re-Ignition Time (Min) (Max)	12 min
Ignition Time (Max)	120 s
Voltage (Max)	150 V
Voltage (Min)	120 V
Voltage (Nom)	135 V

Approval and Application		
Energy Saving Product	Not Applicable	
Mercury (Hg) Content (Max)	52.0 mg	
Luminaire Design Requirements		
Bulb Temperature (Max)	400 °C	
Cap-Base Temperature (Max)	250 °C	
Product Data		
Order product name	MH400/U/ED28 12PK	
EAN/UPC - Product	046677426026	
Order code	426023	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	12	
Material Nr. (12NC)	928601151303	
Net Weight (Piece)	0.001 kg	

#### Mechanical and Housing

Bulb Finish	Clear	
Cap-Base Information	Brass [ Brass Cap]	
Bulb Material	Hard Glass	
Bulb Shape	ED28 [ ED28]	

#### Dimensional drawing



Product	D	C (max)
MH400/U/ED28 12PK	3.5 in	8.313 in



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.