



Switch Start Metal Halide Standard

MH250/U 12PK

High performance, Long life and Superior light quality A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	E39 [Single Contact Mogul Screw]
Operating Position	Universal [Universal]
Main Application	General and Street Lighting
Life to 50% Failures (Nom)	10000 h
ANSI Code HID	M58-/E
Footnotes HID 1	Requires a ballast specified or approved for Philips metal halide lamps, or one that is designed to operate all popular brands of metal halide lamps. 1000W types will operate from H36 conventional lag type ballast for Mercury Vapor lamps at ambient temperatures of 50 degrees F or higher. 1000W types must not be operated at 1500W. (377)

Footnotes HID 2	Rated life: Vertical +/- 15 degrees. Other positions 75% of vertical life. (385)
Footnotes HID 3	Vertical lumens. Horizontal lumens 6%–10% lower. (393)
Light Technical	
Color Code	640 [CCT of 4000K]
Luminous Flux (Rated) (Min)	19125 lm
Luminous Flux (Rated) (Nom)	21250 lm
Color Designation	Cool White (CW)
Design Mean Lumens	13500 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.395
Correlated Color Temperature (Nom)	4000 K

Switch Start Metal Halide Standard

Luminous Efficacy (Rated) (Min)	76.5 lm/W
Luminous Efficacy (rated) (Nom)	85 lm/W
Color Rendering Index (Nom)	65

Operating and Electrical

Lamp Current (Nom)	2.1 A
Ignition Supply Voltage (Min)	350 V
Re-Ignition Time (Min) (Max)	8 min
Ignition Time (Max)	120 s
Voltage (Max)	148 V
Voltage (Min)	118 V
Voltage (Nom)	133 V

Mechanical and Housing

Bulb Finish	Clear
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Bulb Shape	ED28 [ED28]

Approval and Application

Energy Saving Product	Not Applicable
Picogram Per Lumen Hour	215.1 pg/lm.h
Mercury (Hg) Content (Nom)	33 mg


Luminaire Design Requirements

Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	210 °C

Product Data

Order product name	MH250/U 12PK
EAN/UPC - Product	046677274849
Order code	274845
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601150813
Net Weight (Piece)	0.001 kg

Dimensional drawing



MH R 250W/640 E39 ED28 U

Product	D	C (max)
MH250/U 12PK	3.5 in	8.313 in

