



R-085

Protection from Cut, Cold, and Impact



Impact

Abrasion Protection



Cold



Cut



Light Duty

Innovative impact, cut, and protection combined with superior dexterity for ultimate comfort in a variety of end uses

- The Ringers 085 R-Flex Impact glove with Nitrile Half Dip and Fleece Lining combines protection against impact hazards and the highest levels of cut resistance, with added warmth for application in cold environments.
- A breathable knit shell developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- The sandy finish palm ensures secure grip on wet and dry surfaces, and touchscreen compatible index, middle and thumb tips allow technology interaction.



Industries

- Automotive
- Mining
- Oil and gas
- Manufacturing
- Construction
- Automotive Aftermarket

Applications

- Makeup and breakout tools
- Running tools into the wellbore
- Handling explosives
- Assembly of parts
- Engagement and release of drill string slips
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Cold Storage
- Scaffolding
- Loading and hauling
- Assembling and mounting components



R-085

Protection from Cut, Cold, and Impact

Key Features

- Breathable knit shell offers cut resistance
- TPR impact protection on top of hand and full length of fingers
- Palm-dipped nitrile coating on palm with sandy finish for enhanced grip
- Fleece lined for added warmth in cold temperatures
- TCR patch to reinforce wear & tear zone
- Superior grip on wet and dry surfaces
- High visibility for increased safety
- Touchscreen compatible index, middle and thumb tips

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS R085	Finishing: Dipped Coating Material: Nitrile Liner Material: HPPE Cuff Style: Knitwrist	13	8, 9, 10, 11, 12, 13	Hi Viz	• 8 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

