



LED MR16

8.5MR16/LED/830/F25/DIM 12V 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	8.5-75W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	25 °
Luminous Flux (Nom)	620 lm
Luminous Intensity (Nom)	3250 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	72.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	- Hz
Power (Nom)	8.5 W

Lamp Current (Nom)	960 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	ac electronic 12 V

Temperature	
T-Case Maximum (Nom)	100 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh


LED MR16

Product Data

Order product name	8.5MR16/LED/830/F25/DIM 12V 10/1FB
EAN/UPC - Product	046677533175
Order code	929001881404
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001881404
Net Weight (Piece)	0.052 kg


Dimensional drawing




MR16 12V 8-50W 621lm 24D 3000K GU5.3 D

Product	D	C
8.5MR16/LED/830/F25/DIM 12V 10/1FB	50.5 mm	46.5 mm


Photometric data



8-50W GU5-3 MR16 24D 830 3000K





8-50W GU5-3 MR16



8-50W GU5-3 MR16 24D 827 2700K

LED MR16

Lifetime



7-50W GU5-3 MR16

7-50W GU5-3 MR16

