



TECHNICAL DATA

Specifications

Leak Detector (Receiver)

Frequency Response:	40 kHz \pm 2 kHz
Sensitivity Adjustment:	Yes (wheel)
Alarm:	Audible (Ticking) / Visual (LED)
Earphone Jack:	Yes (Earphones included)

Transmitter

Output Frequency:	40 kHz
Power Indicator:	LED

General Specifications

Power Supply:	2 "9V" Batteries
Product Certifications:	CE, RoHS
Operating Temperature:	32 to 104°F (0 to 40°C)
Storage Temperature:	-4 to 122°F (-20 to 50°C)
Dimensions:	Receiver: 7.6 x 2 x 1.2" (192 x 50 x 30 mm)

Weight:

Transmitter: 3.9 x 2.3 x 1.1" (101 x 59 x 28 mm)
Receiver: 4.1 oz (115 g)
Transmitter: 3.2 oz (90 g)

Features

- Locates leaks generated by pressure, vacuum, water, gas or air
- Visible (LED) and Audible (ticking) alarms assist in pinpointing leaks
- Earphone jack for loud environments (earphones included)
- User adjustable sensitivity wheel
- Ultrasonic Transmitter generates a 40 kHz signal
- Includes transmitter, earphones, carrying case and batteries



Model	Description
R9100	Ultrasonic Leak Detector