



OMNIAIRE 2000C

HEPA Air Filtration Machine

ORDERING INFO

OmniAire 2000C	OA2000C
Primary/Secondary Two-Stage Filters (box of 20)	OFP2518
HEPA Filter 99.99%, 0.3 μ (metal frame)	OAH2418G
HEPA FILTER 99.97%, 0.3 μ (pb frame)	OAH2418
Bag Filter Housing (includes 1 Bag Filter)	HBF2000
Bag Filter MERV 15	OBF9
Vapor Trap V-bank Filter	OCVT18
OdorGuard 600 Carbon Filter	OG2418D
Intake Manifold Kit (Manifold, Clamp & 3' Duct)	OAIM2000-12KIT
ABS Plastic Intake Manifold, 12" Dia.	OAIM2000-12
Quick Clamp, 12"-16" Dia.	QCW14
Flexible Duct, 12" Dia. x 25' L	OAD12
Flexible Duct, Wire & Fiber Reinforced	OAD12R

PART NUMBER



UL 507:1997/R:2017-01
CAN/CSA-C22.2 No. 113-15

The OmniAire 2000C is a construction grade HEPA air scrubber, delivering the performance of a full sized negative air unit but is compact and easy to move and set up. The 2000C is used to create positive or negative pressure at asbestos, lead and mold abatement projects, for collection of construction dust from cutting or grinding of concrete, wood or plaster. The HEPA filter can also be replaced with an economical multi-pocket bag filter. Additional accessories include intake manifold, flex ducting and quick clamps.

OmniAire 2000C

Airflow*	900/1600 CFM
Power Requirements	115VAC/60 Hz/10.6 Amp
Motor	1 HP with thermal overload
Controls	speed switch - HIGH/OFF/LOW; amber change filter indicator light; red power indicator light
Filtration	HEPA filter 99.97% @ 0.3 μ ; MERV 9 primary/secondary filter Optional: MERV 15 bag filter; OdorGuard 600 activated carbon web filter; VaporTrap V-bank filter (27 lbs of active carbon); HEPA filter 99.99% @ 0.3 μ
Housing	galvanized metal; silicone sealed before riveting; 12" outlet; (4) rubber grip handles; (2) 5" hospital grade locking casters; (2) 5" rigid casters
Size/Weight	20"W x 32"H x 34"L; 135 lbs.

*Airflows based on blower manufacturer curves. Different filters may cause the flow to vary.