

Product data sheet

Characteristics

9050AO10DV02

Timing Relay, Type A, pneumatic, off delay, 0.1 to 60 seconds, 15A, 600 V, SPDT, timed, 110/120 VAC 50/60 Hz coil, open



Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	Off-delay
Timing Range	0.1 s...1 min
Switch Function	SPDT
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Contact Operation	Time delayed 1 NO + 1 NC
Current rating	15 A

Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 Ms - on-delay 27 ms - off-delay
Mounting Support	Panel

Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	UL Listed CSA
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
GTIN	785901864110
Nbr. of units in pkg.	1
Package weight(Lbs)	27.36 oz (775.643 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.70 in (9.398 cm)
Package 1 width	4.90 in (12.446 cm)
Package 1 Length	6.60 in (16.764 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	50
Package 2 Weight	89.00 lb(US) (40.37 kg)
Package 2 Height	40.00 in (101.6 cm)

Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------