


Electrical Specifications

Output Power (W)	Output Voltage (V)	Output Current (A)	T _{case} Max	Input Current at 120V (A)	Max. Input Power (W)	Inrush Current (A _{pk} /μs)	Max. THD (%)	Min. Power Factor	Surge Protection (KV)	Weight (Lbs)	Envir. Protection Rating
60	12	0.10~5.0	90°C	0.6	70	100/200	20	0.99	2.5	1.4/635	UL Dry & Damp

Wiring Diagram



Input and output use lead-wires.
Lead-wires are 18AWG 105C/600V solid copper

Standard Lead Length


	in.	cm.
Black	9	22
White	9	22
Blue	26	66
Red	26	66
Gray		
Violet		

Maximum Wiring Distance (at full load)

Wire Size (AWG)	Distance (feet)
26	2
24	4
22	6
20	10
18	15
16	24
14	38
12	59
10	100

Revised 05/15/2012

Enclosure



	in. (mm)
Case Length	8.34 (211.8)
Case Width	1.76 (42.5)
Case Height	1.1 (27.9)
Mounting Length	8.99 (228.4)
Mounting Width	1.22 (30.9)
Overall Length	9.45 (240)



UL Class 2
E220165



7310_S-000
3426-32

Xitanium LEDINTA0012V50FO

60W 12V 5.0A

LEDINTA0012V50FO	
Brand Name	XITANIUM
Description	60W 12V 5.0A
Input Voltage	120~277
Input Frequency	50/60Hz
RoHS	Yes
Approbations	UL, CSA
Status	Active

Installation & Application Notes:

Section I – Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105°C rating or higher.

Section II – Performance

- 2.1 LED Driver is UL Class 2 power unit as per UL1310. It is also listed in the UL Sign Accessory Manual (UL SAM).
- 2.2 LED Driver has Class A sound rating.
- 2.3 LED Driver has a minimum operating ambient temperature of -40°C.
- 2.4 LED Driver has a 400 maximum switching cycle between -40°C to -20°C.
- 2.5 LED Driver has a life expectancy of 50,000 hours at Tcase of ≤ 80°C.
- 2.6 LED Driver has a life expectancy of 100,000 hours at Tcase of ≤ 70°C.
- 2.7 LED Driver has a typical self rise of 30°C at maximum load in open air without heat sink.
- 2.8 LED Driver is certified by UL for use in a dry or damp location (Outdoor Type I).
- 2.9 LED Driver tolerates sustained open circuit and short circuit output conditions without damage.
- 2.10 LED Driver maximum allowable case temperature is 90°C – see product label for measurement location.
- 2.11 LED Driver reduces output power to LEDs if maximum allowable case temperature is exceeded.
- 2.12 LED Driver has a failure rate of ≤ 0.01% per 1,000 hours.
- 2.13 LED Driver complies with FCC rules and regulations, as per Title 47 CFR Part 15 Non-Consumer (Class A).

Section III – UL Conditions of Acceptability (File E220165; Vol. 1; Sec. 3)

When installed in the end product, consideration shall be given to the following:

- 3.1 These LED Drivers have been evaluated to comply with Class 2 output criteria.
- 3.2 These Led Drivers are only suitable for use in Dry and Damp locations.
- 3.3 These products are rated as follows:

Model	Input, 60 Hz.			OUTPUT V and Amperes DC
	Volt/V	Amp/A	Power/W	
LEDINTA0012V50FO	120-277	0.60-0.29	60	12V and 5.0A(###)

(###) - For connection to LED array consisting of 60W maximum

- 3.4 In the end product, power supply spacing to other heat producing components shall be minimum 4 inches spacing to sidewalls, and minimum 2 inches spacing to top of enclosure and mounted not closer than 1 in. end to end or 4in. side to side from adjacent LED power supplies.
- 3.5 The units were submitted and tested for a maximum manufacturer's recommended Tc point described in the table below. If adjacent LED power supplies are spaced closer then 1in. end to end or 4 in. side to side a temperature test shall be conducted in the end use product.

Model No.	Input Voltage, Hz	Max. Case @ Tc, °C	Ambient, °C (Reference only)(*)
LEDINTA0012V50FO	120-277,60	90	60.2/60.5

Revised 05/15/2012

Xitanium LEDINTA0012V50FO

60W 12V 5.0A

LEDINTA0012V50FO	
Brand Name	XITANIUM
Description	60W 12V 5.0A
Input Voltage	120~277
Input Frequency	50/60Hz
RoHS	Yes
Approbations	UL, CSA
Status	Active

(*) - 120V/ 277V

Revision History:

Rev No.	Date	Description	Approval	Remarks
1.1	01/17/2012	* Add Envir. Protection Rating	N.T.	
2.1	03/02/2012	*Modify Part #(Remove Dashes)	N.T.	
3.1	04/06/2012	*Add Installation & Application Notes: Section II - 2.4: Max Switching Cycles	N.T.	
4.1	05/15/2012	* Add Approbations: UL, CSA	N.T.	

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

