



105 Series and 1105MAX Series

Mini Air Ratchets



Boost your productivity

105 Series


The Ingersoll Rand 105 Series air ratchet offers professional technicians an outstanding combination of value and performance, delivering impressive comfort and durability.

Unique head construction provides improved durability and more consistent performance over the life of the tool.

Low-profile forward/reverse control has a wide diameter for easy gripping and also eliminates accidentally changing directions in confined spaces.

Ergonomic coupling nut and handle ensure a comfortable grip with no sharp edges.

25 ft-lb max torque and 250 rpm free speed deliver impressive power to get the task at hand done fast.



Specifications

Model	Drive Size	Max Torque ft-lb (Nm)	Avg. Free Speed rpm	Weight lb (kg)	Length in (mm)	Air Cons. cfm (L/min)	Free Speed Sound Level dBA	Air Inlet	Minimum Hose Size
105 SERIES									
105-D2	1/4"	25 (34)	250	1.40 (.64)	7.30 (186)	18 (510)	81.8	1/4"	3/8"
105-D3	3/8"	25 (34)	250	1.40 (.64)	7.30 (186)	18 (510)	81.8	1/4"	3/8"
105-L2*	1/4"	25 (34)	250	1.56 (.71)	8.41 (214)	18 (510)	81.8	1/4"	3/8"
1105MAX SERIES									
1105MAX-D2	1/4"	30 (41)	300	1.43 (.65)	7.36 (187)	20 (566)	88.9	1/4"	3/8"
1105MAX-D3	3/8"	30 (41)	300	1.43 (.65)	7.36 (187)	20 (566)	88.9	1/4"	3/8"

*Extended head offers longer reach.

105 and 1105MAX

1105MAX Series

With the 1105MAX Series air ratchet, you get best-in-class power and speed coupled with superior features to give you MAX power, MAX control, and MAX comfort.

Variable-speed regulator is hand-operable and gives technicians the ability to easily control performance — perfect for use on small fasteners.

Ergonomic coupling nut and composite handle ensure operator comfort even during extended use; composite handle insulates from the cold.

Feather-touch lever gives operators access to all of the performance that lies between Off and On.

Nickel-plated housing provides enhanced corrosion resistance.

30 ft-lb max torque and 300 rpm free speed deliver best-in-class power for stubborn fasteners with the speed to get the job done even faster.



MAX Power

30 ft-lb of torque combined with 300 rpm provides optimal torque/speed combination

MAX Control

Easily accessible variable power regulator combined with feather touch lever offers unprecedented control

MAX Comfort

Ergonomic coupling nut improves handle comfort and composite handle insulates against cold

irtools.com



Socket sets

SK2C10 - 1/4" Drive
Combo Set
SK3H8 - 3/8" Drive
Combo Set

Protective tool boots

103-BOOT

Service kits

1105-D2-TRK1
1105-D3-TRK1

Lubrication

67-1 LB
70 1 LB
10Z4

Ingersoll Rand provides total solutions for getting the job done right. When you need genuine replacement parts, count on us to deliver.



Ingersoll Rand Industrial Technologies provides products, services and solutions that enhance our customers' energy efficiency, productivity and operations. Our diverse and innovative products range from complete compressed air systems, tools and pumps to material and fluid handling systems and environmentally friendly microturbines. We also enhance productivity through solutions created by Club Car®, the global leader in golf and utility vehicles for businesses and individuals.

(800) 866-5457 • irtools.com

Distributed by:

