



- NOTE 1. Arm : S45C + Chrome Plating  
 2. To swage it after tighten  
 Nut : S35C or similar material  
 Holder : SDG400-C + Black Chromate  
 3.To keep smoothly rotating

DIMENSION	TOLERANCE	APPROVED	UNITS	PARTS NAME
TO 6	±0.1	<b>Toshi</b>	mm	<b>Hook attachment</b>
OVER 6 TO 30	±0.2	CHECKED	MATERIAL	
OVER 30 TO 120	±0.3	<b>MO</b>	-	MODEL
OVER 120 TO 400	±0.5	DRAWN	QUANTITY	FGC,FGN-0.2~50
OVER 400 TO 1000	±0.8	<b>YS</b>	1	FGX - 10
OVER 1000 TO 2000	±1.2		SCALE	CODE
OVER 2000 TO 4000	±2.0		1 : 1	<b>BFGB0250010 (EF450008-0)</b>
HEAT TREATMENT / HARDNESS		DATE	02/27/2017	DRAWING NO.
SURFACE TREATMENT		<b>NIDEC-SHIMPO AMERICA CORP</b>		<b>BGBM054</b>
NOTE 1				