

PLATFORM TRUCKS



BASE WEIGHT STANDARD SPECIFICATIONS

BED SIZE	SMOOTH/CARPET	TREAD
24 x 36	29	30
24 x 42	32	33
24 x 48	36	37
24 x 60	42	43
30 x 48	41	42
30 x 60	47	48
30 x 72	54	56
36 x 48	47	49
36 x 60	55	57
36 x 72	63	65

(base weight = one handle, no casters)

- Heavy-duty light aluminum
- Designed for tough job service, load handling, versatility and long life
- One handle standard with a height of 26 1/2" from the base of the platform (second handle optional)
- Durable extruded corner sockets integrated with frame so handle fits tightly and securely
- 1,600 to 3,000 pound capacity
- Reinforced box-frame construction for strength and durability
- Caster brake option can be safely activated for maximum load control

ACCESSORIES



Handle Cross Braces

Two cross braces per handle help hold load in place.

Available in 24", 30" and 36" widths.



Carpeted Deck

Protects cargo and maintains a professional appearance.



Caster Brake

5" 86067 - 8" 86069

Foot-operated, friction-type brake engages tire surface.

Attaches to swivel caster.



Full Perimeter Rubber Bumpers

Reduce damage to walls with non-marking, metal reinforced gray rubber bumpers.

(1 1/8" wide by 1" deep).

PLATFORM TRUCK CASTERS



Part #86135 – 5" x 2"

Part #86151 – 8" x 2"

Black thermoplastic rubber on a polyolefin core. Easy to push and roll with flat, hard tread. Limited noise absorption. Performs well on all surface conditions.



Part #86137 – 5" x 2"

Part #86139 – 8" x 2"

Gray thermoplastic rubber on a polyolefin core. Round tread, non-marking, good shock and noise absorption. Easy starting and rolling.



Part #86138 – 5" x 2"

Part #86152 – 8" x 2"

Red polyurethane on a polyolefin core. Resistant to water, chemicals and solvents. Hard tread for easy rolling. Limited noise absorption. Performs well on all surface conditions.



Part #86067 – 5"

Part #86069 – 8"

Foot-operated, friction-type brake engages tire surface. Attaches to swivel caster.

CASTER KIT**		WHEEL CONSTRUCTION							SWIVEL CASTER			RIGID CASTER	
A = 1 BRAKE B = 2 BRAKES	SIZE DIA. x WIDTH	CAPACITY SET OF 4 (LBS.)	TREAD HARDNESS	TREAD COLOR	HUB COLOR	BEARING TYPE	TEMP. RANGE	LOAD HEIGHT	PART NO. (B = BRAKE)	SWIVEL RADIUS	APPROX. WGT.*(LBS.)	PART NO.	APPROX. WGT.*(LBS.)
86135 86135A 86135B	5" x 2"	1,600	65 ±5 durometer A-scale	black	light gray	Roller	-45° to +180°F	6½"	13057 13057B	4¼ 4¼	4.35 4.95	13058	3.55
86151 86151A 86151B	8" x 2"	2,800	65 ±5 durometer A-scale	black	light gray	Roller	-45° to +180°F	9½"	130076 130076B	6 6	5.8 6.6	130075	4.95
86137 86137A 86137B	5" x 2"	1,600	65 ±5 durometer A-scale	light gray	light gray	Roller	-45° to +180°F	6½"	13053 13053B	4¼ 4¼	4.2 4.8	13054	3.45
86139 86139A 86139B	8" x 2"	2,800	65 ±5 durometer A-scale	light gray	light gray	Roller	-45° to +180°F	9½"	13063 13063B	6 6	5.55 6.35	13064	4.7
86138 86138A 86138B	5" x 2"	3,000	55 ±5 durometer A-scale	maroon	light gray	Roller	-45° to +180°F	6½"	13059 13059B	4¼ 4¼	4.4 5	13060	3.6
86152 86152A 86152B	8" x 2"	3,000	55 ±5 durometer D-scale	maroon	light gray	Roller	-45° to +180°F	9½"	130077 130077B	6 6	6.05 6.85	130078	5.2

* Caster only

** All Caster Kits include 2 rigid and 2 swivel casters and attaching hardware.