

# PCA® Spray Faucet Attachment - 0.5 gpm max Pressure Compensating Regular Size



flow, stop and go®

## Features and Benefits

- ▶ Watercolours® design: Color coding to identify flow rate and stream pattern.
- ▶ Provides non-splashing, non-aerated spray.
- ▶ Pressure compensating for constant flow from 20 to 80 psi.
- ▶ Anti-clogging dome screen filters sediment and particles.
- ▶ Compatible with regular and vandal proof M22 & M24 metric housings.
- ▶ Available housing finishes: chrome, polished brass, brushed nickel and oil rubbed bronze.
- ▶ Laser marked housings with statutory marks.

## Certifications

ANSI/NSF®-61-372  
ASME A112.18.1M and CSA B125  
Meets **CALGreen** requirements



## Thread & Part Number

Part #	Designation	Thread Size	Qty.
5504505	Insert only		1
5500005	Regular male	15/16"-27	1
5500505	Regular female	55/64"-27	1
5501005	Regular dual thread	15/16"-27 x 55/64"-27	1
5505203	Regular dual thread	15/16"-27 x 55/64"-27	6
5501004	Regular dual thread	15/16"-27 x 55/64"-27	50
5502305	Vandal proof regular male	55/64"-27	1
5502605	Vandal proof regular dual thread	15/16"-27 x 55/64"-27	1
5505706	Vandal proof regular dual thread	15/16"-27 x 55/64"-27	40

## Color Code

Dome	Flow Regulator	Basket
Natural	Lime Green	Light Gray

## Flow Rate Curve



## Dimensions

No	mm	In
A	20.85	.821
B	13.00	.512
C	19.95	.785
D	≈ 25	≈ 1

## Housings





## Technical Data

Materials: Body Acetal  
O-ring EPDM  
Washer EPDM

Continuous

Short-term (5 minutes max.)  
Per ASME A112.18.1 testing requirements.



NEOPERL, Inc., Waterbury, CT • Tel: 203-756-8437 • Fax: 203-574-2107 • www.neoperl.com