



products meet or exceed applicable ANSI/BIFMA standards

MODEL 510 SHOWN



SPECS:

- Electromagnetically welded seat back
- Features 19-gauge 7/8" round tubular frame with 2 1/2" frame strengthener
- Powder-coated frame
- Two 19-gauge 5/8" U-shaped double riveted cross braces
- Single hinges on each side for added stability and durability
- Color coordinated V-tip plugs for added stability
- Color coordinated polypropylene glides
- Seat with a waterfall front for added comfort
- Warranty Info

DIMENSIONS:


OVERALL: 29 1/4"H x 18 1/4"W x 18 1/2"D

FOLDED: 38"H x 18 1/4"W x 2"D

SEAT: 16 3/4"H x 15 3/4"W x 16"D

BACK: 8 3/4"H x 18 1/4"W

COLOR OPTIONS



AVAILABLE ACCESSORIES



USE WITH:

Model #84
Double-Tier Hanging
Chair Truck

CAPACITY: HOLDS UP TO 84 FOLDING CHAIRS (50 SERIES)

Model #DY35/#DY50
Folding Chair Dolly

CAPACITY: DY35 HOLDS UP TO 35 FOLDING CHAIRS (50 SERIES)
DY50 HOLDS UP TO 50 FOLDING CHAIRS (50 SERIES)

FOR VERTICAL FOLDING STORAGE



National Public Seating



480lb. weight capacity!