



2145QiMAX 3/4" Air Impactool™

Maximum Impact



Maximum Impact

More power. Less air. Not only does the new Ingersoll Rand 2145QiMAX Impactool™ deliver incredible performance and industrial-grade durability, its efficient air motor also reduces air consumption — which saves you money.

MAX Power

1350 ft-lb maximum reverse torque from a tool that weighs just 7.4 lbs and is compact enough to access tight spaces

MAX Durability


Built to last and designed to withstand tough use in rugged environments; a **two-year limited warranty is standard**

MAX Productivity

An air motor that's 16% more efficient than its predecessor and **an easy-to-clean inlet screen** means less downtime, better tool performance, and less money spent on compressed air

Specifications	2145QiMAX*	2155QiMAX
Drive	3/4"	1"
Max Torque (Reverse)	1350 ft-lb (1830 Nm)	1350 ft-lb (1830 Nm)
Forward Torque Range	200 – 900 ft-lb (271 – 1220 Nm)	200 – 900 ft-lb (271 – 1220 Nm)
Blows Per Minute	1150	1150
Maximum Free Speed	7000 rpm	7000 rpm
Sound Pressure (free speed)	91.1 dBA	91.1 dBA
Net Weight	7.4 lb (3.4 kg)	7.4 lb (3.4 kg)
Overall Length	8.5" (217 mm)	8.8" (225 mm)
Air Requirements		
Average Air Consumption	8.5 cfm (241 L/min)	8.5 cfm (241 L/min)
Air Consumption @ load	32 cfm (906 L/min)	32 cfm (906 L/min)
Air Inlet	1/2" NPTF	1/2" NPTF
Min Hose Size	1/2" (13 mm)	1/2" (13 mm)

*Available in 3" and 6" extended anvils.




Assembly and Disassembly of machinery and heavy equipment



Vehicle Service



Equipment Maintenance



2145QiMAX



2145QiMAX-3
3" extended anvil



2145QiMAX-6
6" extended anvil



2155QiMAX

2145QiMAX

The original, perfected twin-hammer mechanism utilizes proprietary advanced metallurgy

Patented four-position power regulator dial provides a range of forward power settings

Patented one-hand forward/reverse for easy operation

Steel hammer case provides excellent durability

Feather-touch trigger enables impressive control

New ergonomic housing increases operator comfort

Innovative new steel wear plate protects the end plate and provides extreme wear resistance

New 7-vane motor delivers more power yet consumes 16% less air

Inlet prescreen captures debris and is easily serviced by tool operators

▶ PATENTED QUIET TOOL TECHNOLOGY reduces sound levels without compromising best-in-class power performance

ingersollrandproducts.com/2145QiMAX



Ingersoll Rand (NYSE:IR) advances the quality of life by creating and sustaining safe, comfortable and efficient environments. Our people and our family of brands—including Club Car®, Ingersoll Rand®, Schlage®, Thermo King® and Trane®—work together to enhance the quality and comfort of air in homes and buildings; transport and protect food and perishables; secure homes and commercial properties; and increase industrial productivity and efficiency. Ingersoll Rand products range from complete compressed air systems, tools and material and fluid handling systems. The diverse and innovative products, services and solutions enhance our customers' energy efficiency, productivity and operations. Ingersoll Rand is a \$14 billion global business committed to a world of sustainable progress and enduring results. For more information, visit ingersollrand.com or ingersollrandproducts.com.



www.ingersollrandproducts.com

Distributed by:

Ingersoll Rand, IR and the IR logo are trademarks of Ingersoll Rand, its subsidiaries and/or affiliates. All other trademarks are the property of their respective owners. Nothing contained on these pages is intended to extend any warranty or representation, expressed or implied, regarding the product described herein. Any such warranties or other terms and conditions of sale of products shall be in accordance with Ingersoll Rand's standard terms and conditions of sale for such products, which are available upon request.

Product improvement is a continuing goal at Ingersoll Rand. Designs and specifications are subject to change without notice or obligation.