

600 Series

BLOW MOLDED RESIN PLASTIC FOLDING CHAIR



products meet or exceed applicable ANSI/BIFMA standards

MODEL 602 SHOWN



SPECS:

- Features 19-gauge steel with metal underbracing on seat for added durability
- Two cross braces for strength
- Powder-coated frame
- Single hinges on each side for added stability and durability
- Lightweight indoor/outdoor use
- Contoured seat and back for comfort
- UV Protected

DIMENSIONS:

OVERALL: 32" H X 18 3/4" W X 21 1/2" D

FOLDED: 42 1/2" H X 18 3/4" W X 3" D

SEAT: 18" H X 15 3/4" W X 16 5/8" D



BACK: 9 1/4" H X 18 3/4" W



300lb. weight capacity!

PLASTIC / FRAME COMBINATIONS

	#602 SPECKLED GREY PLASTIC / GREY TEXTURED FRAME
	#604 BLUE PLASTIC / BLACK FRAME
	#640 RED PLASTIC / BLACK FRAME



EXT-8 Extension Bar required for 600 Series on Model #84 (88" DOOR HEIGHT CLEARANCE)

USE WITH:

Model #EXT-8 Extension Bar for Model #84

Model #84 Double-Tier Hanging Chair Truck
CAPACITY: HOLDS UP TO 60 FOLDING CHAIRS (600 SERIES) WITH EXT-8

Model #DV35/#DV50 Folding Chair Dolly

CAPACITY: DV35 HOLDS UP TO 28 FOLDING CHAIRS (600 SERIES) DV50 HOLDS UP TO 40 FOLDING CHAIRS (600 SERIES)

FOR VERTICAL FOLDING STORAGE

AVAILABLE ACCESSORIES

#PGC1 GANGING DEVICE

GLIDES

#MGC1 GANGING DEVICE

V-TIPS

National Public Seating



800.261.4112 | www.nationalpublicseating.com