



Universal Fit
Pipette Tips

Engineered for precision, clarity and purity.
ENGINEERED FOR PRECISION, CLARITY AND PURITY.

globe[®]
SCIENTIFIC INC.

www.globescientific.com

Universal Fit Pipette Tips



ALL tips are certified free from Human DNA, DNase, RNase, Pyrogens and PCR Inhibitors.

- Manufactured in a cleanroom using fully automated equipment
- No silicone additives, lubricants or heavy metals are used during manufacturing so the possibility of sample contamination is eliminated
- Produced from medical grade virgin polypropylene (PP)
- All tips are graduated to minimize any risk of errors during sample aspiration
- Universal fit design provides an airtight fit on most brands of pipettors
- Available in self-standing bags, racks and reloading stacks



EXCLUSIVE!

First ever bulk pipette tips in
SELF-STANDING BAGS!

This premium quality line of pipette tips is available in these super convenient reach-in bags. Designed for ease-of-use on the benchtop, the bags are self-standing and resealable to keep out dust and particles when not in use.

Say goodbye to spilling tips all over the benchtop!


Low Retention Tips



ALL tips are certified free from Human DNA, DNase, RNase, Pyrogens and PCR Inhibitors.

Engineered for maximum sample recovery and precision.

- The ideal tip for minimum sample and reagent retention
- Tips feature a super clear and ultra-low binding, hydrophobic surface that is achieved using special resins and state-of-the-art molding equipment
- Perfect for highly sensitive PCR and microbiology applications
- Available non-sterile in bags, and sterile in racks and reloading stacks



Tips shown actual size

Ordering Information

Item #	Volume Range	Tip Length	Tip Color	Sterility	Packaging	Unit
150030	0.1 - 10µl	31mm	Natural	–	Bulk in Bag	1000 Tips/Bag
150030RS	0.1 - 10µl	31mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150030RFS	0.1 - 10µl	31mm	Natural	Sterile	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
150040	0.1 - 20µl	45mm	Natural	–	Bulk in Bag	1000 Tips/Bag
150040RS	0.1 - 20µl	45mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150040RFS	0.1 - 20µl	45mm	Natural	Sterile	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
150050	1 - 200µl	54mm	Natural	–	Bulk in Bag	1000 Tips/Bag
150050RS	1 - 200µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150050RFS	1 - 200µl	54mm	Natural	Sterile	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
150053	100 - 1250µl	84mm	Natural	–	Bulk in Bag	1000 Tips/Bag
150053RS	100 - 1250µl	84mm	Natural	Sterile	Racked	96 Tips/Rack, 6 Racks/Box
150053RFS	100 - 1250µl	84mm	Natural	Sterile	Reloading Stack	96 Tips/Tray, 5Trays/Stack



Available in:



Bulk in bags,
non-sterile



Racks, sterile



Reloading stacks, sterile

Low Retention FILTER Tips

Maximum accuracy and protection from contamination.

- Specially designed high quality filter protects pipettors and samples from contamination
- Tips feature a super clear and ultra-low binding, hydrophobic surface that is achieved using special resins and state-of-the-art molding equipment
- Perfect for highly sensitive PCR and microbiology applications
- Available sterile in racks




ALL tips are certified free from Human DNA, DNase, RNase, Pyrogens and PCR Inhibitors.

Tips shown actual size



Ordering Information

Item #	Volume Range	Tip Length	Tip Color	Sterility	Packaging	Unit
150800	0.1 - 10µl	31mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150805	0.1 - 10µl	45mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150810	1 - 20µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150814	1 - 50µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150815	1 - 100µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150820	1 - 200µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
150835	1 - 1000µl	84mm	Natural	Sterile	Racked	96 Tips/Rack, 6 Racks/Box



Standard Tip

Globe Scientific
Low Retention Tip

◀ The super hydrophobic internal surface of our low retention tips optimize liquid flow for maximum sample recovery and accuracy.

Available in:



Racks, sterile

General Purpose

Tips



ALL tips are certified free from Human DNA, DNase, RNase, Pyrogens and PCR Inhibitors.

An excellent choice for all routine applications.

- Produced on state-of-the-art, fully automated production equipment
- Available non-sterile in bags, sterile or non-sterile in racks, and non-sterile in reloading stacks

Tips shown actual size



Ordering Information

Item #	Volume Range	Tip Length	Tip Color	Sterility	Packaging	Unit
151154	0.1 - 10µl	31mm	Natural	–	Bulk in Bag	1000 Tips/Bag
151154R-96	0.1 - 10µl	31mm	Natural	–	Racked	96 Tips/Rack, 10 Racks/Box
151154RS-96	0.1 - 10µl	31mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
151154RF	0.1 - 10µl	31mm	Natural	–	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
151145	0.1 - 20µl	45mm	Natural	–	Bulk in Bag	1000 Tips/Bag
151145R-96	0.1 - 20µl	45mm	Natural	–	Racked	96 Tips/Rack, 10 Racks/Box
151145RS-96	0.1 - 20µl	45mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
151145RF	0.1 - 20µl	45mm	Natural	–	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
151150	1 - 200µl	54mm	Natural	–	Bulk in Bag	1000 Tips/Bag
151150R-96	1 - 200µl	54mm	Natural	–	Racked	96 Tips/Rack, 10 Racks/Box
151150RS-96	1 - 200µl	54mm	Natural	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
151150RF	1 - 200µl	54mm	Natural	–	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
151150Y	1 - 200µl	54mm	Yellow	–	Bulk in Bag	1000 Tips/Bag
151150YR-96	1 - 200µl	54mm	Yellow	–	Racked	96 Tips/Rack, 10 Racks/Box
151150YRS-96	1 - 200µl	54mm	Yellow	Sterile	Racked	96 Tips/Rack, 10 Racks/Box
151150YRF	1 - 200µl	54mm	Yellow	–	Reloading Stack	96 Tips/Tray, 10 Trays/Stack
151153	100 - 1250µl	84mm	Natural	–	Bulk in Bag	1000 Tips/Bag
151153R-96	100 - 1250µl	84mm	Natural	–	Racked	96 Tips/Rack, 6 Racks/Box
151153RS-96	100 - 1250µl	84mm	Natural	Sterile	Racked	96 Tips/Rack, 6 Racks/Box
151153RF	100 - 1250µl	84mm	Natural	–	Reloading Stack	96 Tips/Tray, 5 Trays/Stack
151153B	100 - 1250µl	84mm	Blue	–	Bulk in Bag	1000 Tips/Bag
151153BR-96	100 - 1250µl	84mm	Blue	–	Racked	96 Tips/Rack, 6 Racks/Box
151153BRS-96	100 - 1250µl	84mm	Blue	Sterile	Racked	96 Tips/Rack, 6 Racks/Box
151153BRF	100 - 1250µl	84mm	Blue	–	Reloading Stack	96 Tips/Tray, 5 Trays/Stack

Available in:



Bulk in bags, non-sterile



Racks, sterile; non-sterile



Reloading stacks, non-sterile



Say goodbye to
spilling tips all over the benchtop!



Packaging Options

Convenient Self-Standing Bags **EXCLUSIVE!**

- All bags are self-standing and provide easy access and convenience. This special design helps to prevent bulk tips from spilling out of the bag when left on the bench top
- Each bag features a tamper-evident seal and is recloseable to keep out dust and particles
- Economical packaging choice
- 1000 tips per bag

Color Coded Racks

- Color coded trays for easy tip identification
- Hinged lid keeps dust and particles out
- 8 x 12 format for use with single and multi-channel pipettors
- Fully autoclavable
- Stackable
- Reusable - accepts trays from our reloading stacks
- 96 tips per rack

Economical Reloading Stacks

- The quick, easy, economical and environmentally friendly method for refilling racked pipette tips
- Reloading stacks are designed to snap into racks with minimal effort
- 8 x 12 format for use with single and multi-channel pipettors
- Vertical packaging format conserves storage space
- Fully recyclable cardboard sleeves minimize packaging waste
- Color coded for easy tip identification
- 96 tips per tray; 5 or 10 trays per stack (depending on tip volume)

(Reloading stacks are not available for filter tips)



Empty Racks

Convenient solution for purchase when starting out with our reloading stacks



Item #	Description	Unit
150010	Empty Rack for use with 10uL Pipette Tips and Refill Plates	10 Racks/Box
150012	Empty Rack for use with 200uL Pipette Tips and Refill Plates	10 Racks/Box
150014	Empty Rack for use with 1000uL/1250uL Pipette Tips and Refill Plates	6 Racks/Box

globe[®]
SCIENTIFIC INC.

Customer service, sales and technical support:

Phone: 1 (800) 394-4562 • 1 (201) 599-1400

Fax: 1 (201) 599-1406 • E-mail: mail@globescientific.com