



LGR 6000Li DEHUMIDIFIER



QUIET, FAST DRYING AND ULTIMATE MOISTURE CONTROL


- **Extreme Dew Point Technology** delivers sensor-driven, optimized response to changing conditions – for optimal drying
- **Command Hub touchscreen** provides humidistat, inlet and outlet temp and humidity conditions, plus firmware updates and 24/7 monitoring and control using free mobile app
- **Truly fast 4-bolt access** for cleaning and preventative maintenance
- **Amazingly quiet AND powerful!**
- **Maximum drying or humidity control** – at your fingertips!

BUILT IN USA
WITH GLOBALLY SOURCED MATERIALS



Features the 4-PRO™ Filter that protects in 4 ways!

The ONLY electrostatic dehumidifier filter with antimicrobial treated filter media* and carbon for odors!




GET THE DEHU THAT'S POWERFUL, COMPACT AND QUIETER!



SEE IT IN ACTION!

*EPA #071027-MEX-001

DRYING SET-UP



TEAM DEHUMIDIFIERS WITH AIRMOVERS FOR BEST RESULTS

LGR 6000Li

MODEL	492T29
WATER REMOVAL (MAX.)	204 PTS. 96.5 LITERS / DAY
PROCESS AIR	320 CFM 544 CMH
AMPS	6.6A
WEIGHT	103 LBS. 46.7 KG
DIMENSIONS (H x D x W)	32.1 x 19.8 x 20.0 IN. 81.5 x 50.3 x 50.8 CM



EnvironmentsHQ.com

AVAILABLE THROUGH

GRAINGER

FOR THE ONES WHO GET IT DONE