

DEWALT

20V MAX*
LITHIUM ION **XR**
BRUSHLESS

2.6 JOULES
AND 1500 RPM**
For fast and efficient drilling,
even in the hardest concrete

**BRUSHLESS
MOTOR**

Provides long run time in
demanding applications



**THREE MODE
OPERATION**
For Rotary Hammer Drilling,
Chipping and Drill only

**CORDED
MECHANISM**
Quad seals for long service
life and performance

**4.0 AH HIGH
CAPACITY PACK**
Provides long
run time

**SDS+ TOOL
HOLDER**
Optimized drilling range
between 5/32" and 5/8"

INCLUDES



DCB204 (4.0 AH)



DCB115

*Maximum initial battery voltage
(measured without a workload) is 20
volts. Nominal voltage is 18.

**According to EPTA-Procedure 05/2009

DEWALT
ENGINEERED BY POWERS

FASTENERS 5/32"-5/8" FOR OPTIMAL USE



TAPPER+®



**SNAKE+
ANCHOR**



**HANGERMATE+
ANCHOR**



POWER-STUD+™



**SCREW-BOLT+
ANCHOR**



**POWER BOLT+
ANCHOR**



**20V MAX* XR® BRUSHLESS SDS+ D-HANDLE
ROTARY HAMMER KIT**

DCH133M2

SPECIFICATIONS

No Load Speed	0-1500 rpm
BPM	0-5550 bpm
Optimal Drilling in Concrete	3/16"-5/8" (5 mm - 16 mm)
Impact Energy	2.6 Joules**
Chipping	Yes
Tool Length	15"
Tool Weight (Tool only)	4.6 lbs (2.1 kg)

TOOL WARRANTY



BATTERY WARRANTY



100+ PRODUCTS

OUR FASTEST GROWING SYSTEM



YOUR FIRST LINE OF DEFENSE.™

REDUCES SILICA DUST EXPOSURE WHILE DELIVERING THE PERFORMANCE YOU EXPECT.

RELATED PRODUCTS



DCH133B
20V MAX* XR CORDLESS
LITHIUM-ION ROTARY HAMMER



D25301D
DUST EXTRACTOR
TELESCOPE



DW5471
5/8" X 8" X 10" ROCK CARBIDE
4CUTTER SDS PLUS HAMMER BIT



PFM2211200
HANGERMATE+ FOR CONCRETE -
INTERNALLY THREADED

www.DEWALT.com 1-800-4-DEWALT

Copyright ©2017 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.