

# Magnifier luminaire Ring LED

113142M10



<b>light source</b>	LED
<b>work equipment</b>	electronic plug-in transformer
<b>connected load</b>	100-240 V; 50/60 Hz
<b>power consumption</b>	approx. 6 W
<b>luminous flux</b>	approx. 420 lm
<b>luminous efficiency</b>	approx. 70 lm/W
<b>light type/color</b>	cold white
<b>color temperature</b>	approx. 4,000 K
<b>color rendering index</b>	CRI > 90; R9 > 50
<b>light distribution</b>	direct
<b>direct ratio</b>	approx. 100%
<b>color rendering index</b>	CRI > 90; R9 > 50
<b>chromaticity tolerance LED</b>	< 3 SDCM
<b>system of protection</b>	IP 20
<b>class of protection</b>	II
<b>technology</b>	continuously dimmable
<b>operation</b>	touch-LED
<b>housing</b>	aluminum/plastic; anodized; black
<b>cover</b>	acrylic (PMMA); satine
<b>arm</b>	aluminum colored anodized
<b>mains lead</b>	built-in plug; 2.30 m (90")
<b>fastening</b>	table clamp (accessory); wall bracket (accessory); screw-down flange
<b>lens, dimensions</b>	ø 72 mm
<b>lens, diopters</b>	6




NEMA 1-15P

## illuminance

measuring conditions: d=15cm

Em: 2663 lx  
Emax: 5282 lx  
Emin: 813 lx



## luminous intensity

