# DEWALT

# FLEX/OLT

**POWER** OF CORDED. | **FREEDOM** OF CORDLESS:

#### 6.1 JOULES\*\* AND 540 RPM

For fast and efficient drilling, even in hard concrete

## SHOCKS

SHOCKS ACTIVE VIBRATION CONTROL SYSTEM® reduces vibration felt by the user at the handles

## E-CLUTCH

The DEWALT E-Clutch® system senses the motion of the tool and reduces the motor torque to a manageable level if necessary

#### SDS MAX TOOL HOLDER

Optimized drilling range between 1/2" and 1-1/8"

## CORDED — MECHANISM

For long service life and high performance



DEWALT's Perform & Protect™ line of tools is designed to provide a high level of one or more of the following: control, dust containment or low vibration, without sacrificing performance.

\*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

DEWAL

\*\*According to EPTA-Procedure 05/2009

FEFFFFF





FLEXVOLT

DCB609 (9.0 AH)



**DCB118** 

### SEE FULL RANGE OF DEWALT ADHESIVES AT WWW.ANCHORS.DEWALT.COM



High Strength Epoxy 1:1 & 3:1 Cartridges



Hybrid Acrylic Epoxy 10:1 Cartridges



#### **SPECIFICATIONS**

| No Load Speed             | 0-540 rpm                 |
|---------------------------|---------------------------|
| ВРМ                       | 0-3150 bpm                |
| Optimal Drilling<br>Range | 1/2"-1 1/8"<br>(12-28 mm) |
| Impact Energy             | 6.1 Joules**              |
| Chipping                  | Yes                       |
| Vibration Measurement     | 9.4 m/s <sup>2</sup>      |
| Tool Weight (Tool only)   | 11.91 lbs (5.4 kg)        |
|                           |                           |







#### **RELATED PRODUCTS**











## www.DEWALT.com 1-800-4-DEWALT

Copyright ©2017 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.