

DEWALT

GUARANTEED TOUGH.

MADE IN THE ★★★★★
USA
WITH GLOBAL MATERIALS
LOOK FOR THIS LOGO ON SPECIALLY MARKED DEWALT PACKAGES.

**PERFORM
PROTECT™**

E-CLUTCH™

E-CLUTCH® SYSTEM
Activates in Less Than a Tenth of a Second When a Pinch/Stall Event is Detected.

**HIGH POWER
13 AMP MOTOR**
Powerful 1700 Watt Motor Offers Lower Field Case Temperatures to Improve Durability*

DUST EJECTION SYSTEM™
Contributes to Long Motor Life

**LANYARD
READY™**

Lanyard Ready™ Compatible
Lanyard Ready™ Connection Point Available as a Part Through Service for No Lock-On Models Only

TWO STAGE TRIGGER
Requires Two Actions to Activate Tool. Lock-On and No Lock-On Versions Available.

SEPARATE BRUSH DOORS
Allows for Easy Access to Brushes for Quick Changes

PIPELINE GEAR CASE COVER
Gear Case Grip Allows Gear Case to be Gripped as a Handle While Performing Specific Applications as Noted in the Instruction Manual.

ONE-TOUCH™ COMPATIBLE GUARD
Simple Lever Change Allows Unit to be One-Touch™ or Two-Touch for Guard Adjustments. Includes 5" and 6" Type 27 and 6" Type 1 Guards.

INCLUDES

- (1) 5" (125 mm) Type 27 Guard
- (1) 6" (150 mm) Type 27 Guard
- (1) 6" (150 mm) Type 1 Guard

COMPATIBLE WITH

DUST



DWE46152
5" SURFACE GRINDING
DUST SHROUD



DWE46100
5"/6" CUTTING &
TUCKPOINTING DUST
SHROUD

*As compared to previous 13 Amp DEWALT Small Angle Grinder Models

5" (125 mm) / 6" (150 mm) HIGH PERFORMANCE GRINDER WITH NO LOCK-ON TRIGGER GRIP

DWE43066N

SPECIFICATIONS | DWE43066N

Amps	13.0 AC Amps
Max Watts Out/ Max Horsepower	1,700 W/2.3HP
No Load Speed	9,000 RPM
Spindle Thread	5/8"-11
Switch Type	Trigger
Dust Ejection System	Yes
Tool-Free Flange System	Yes
E-CLUTCH® System/ Overload Protection	Yes
Tool Length (inches)	16.5
Tool Weight	5.7 lbs.
Power Loss Reset	Yes
Lanyard Ready™	Compatible*

TOOL WARRANTY

3 YEAR	1 YEAR	90 DAY
LIMITED WARRANTY	FREE SERVICE	MONEY BACK GUARANTEE



RELATED PRODUCTS



6" (150MM) HIGH PERFORMANCE TRIGGER SWITCH GRINDER



4-1/2"(115MM)- 5" (125MM) HIGH PERFORMANCE TRIGGER SWITCH GRINDER



4-1/2"(115MM)- 5" (125MM) HIGH PERFORMANCE TRIGGER SWITCH GRINDER W/ NO LOCK ON



4-1/2" - 5" HIGH PERFORMANCE TRIGGER GRIP GRINDER

SPECIFICATIONS	DWE43066	DWE43115	DWE43115N	DWE46166N
Amps	13.0 AC Amps	13.0 AC Amps	13.0 AC Amps	13.0 AC Amps
Max Watts Out/ Max Horsepower	1,700 W/2.3HP	1,700 W/2.3HP	1,700 W/2.3HP	1,700 W/2.3HP
No Load Speed	9,000 RPM	11,000 RPM	11,000 RPM	9,000 RPM
Spindle Thread	5/8"-11	5/8"-11	5/8"-11	5/8"-11
Switch Type	Trigger	Trigger	Trigger	Trigger
Dust Ejection System	Yes	Yes	Yes	Yes
Tool-Free Flange System	Yes	Yes	Yes	Yes
E-Clutch® System/ Overload Protection	Yes	Yes	Yes	Yes
Tool Length (inches)	16.5	16.5	16.5	16.5
Tool Weight	5.7 lbs.	5.7 lbs.	5.7 lbs.	7.0 lbs.
Power Loss Reset	Yes	Yes	Yes	Yes
Lanyard Ready™	No	No	Compatible*	Yes

*Lanyard Ready™ Connection Point Available as a Part Through Service for No Lock-On Models Only

Dealer Stamp

1-800-4DEWALT

www.DEWALT.com

Copyright ©2017 DEWALT. The following are examples of trademarks for one or more DeWALT power tools and accessories: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

ICDWE43066NSS