LED Replacement Lamps

2-Pin Plug-in Lamps



Project Name	
Date	Туре
Notes	

Provides a plug & play solution to leverage the low energy and long life of LED. Simply plug the LED lamp into the existing fixture, no tools, wiring, or costly upgrades required.

PERFORMANCE HIGHLIGHTS:

CFL PLUG IN LAMPS				
Light Output Range:	500-1050 Lumens			
CRI:	80			
CCT:	2700K, 3000K, 3500K, 4000K & 5000K			
Efficiency:	Up to 113 LPW			
Wattage:	5W & 10.5W			
Life:	50,000 hours L70			
Temperature Rating:	-20°C to 45°C			
Rating:	Damp			

LIMITED WARRANTY

5 Years

FEATURES:

- Lasts 5X longer than CFL
- 50,000 hours rated life (L70)
- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

BENEFITS:

Energy + Cost Savings

- Uses 50% less energy than CFL
- 5W LED saves over \$44 in energy vs 13 watt CFL
- 10.5W LED saves over \$41 in energy vs 18 watt CFL
- Energy savings based on \$0.11 per kWh over the rated life of the lamp
- Rated for enclosed or open fixtures

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.





LED Replacement Lamps

2-Pin Plug-in Lamps

Project Name _ Date _


Notes _

_ Type_

Spec Table

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)		# Location Rating	Additional Information
	2-PIN														
	GX23	5	91404	LED5GX23/827	#	6	6.7	500	2700	80	13	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	GX23	5	91405	LED5GX23/830	#	6	6.7	530	3000	80	13	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
Plug	GX23	5	91407	LED5GX23/835	#	6	6.7	545	3500	80	13	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	GX23	5	91408	LED5GX23/840	#	6	6.7	560	4000	80	13	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	GX23	5	91410	LED5GX23/840	#	6	6.7	565	5000	80	13	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	HORIZONTAL 2-PIN														
	G24d	10.5	92994	LED11G24d-H/827	#	6	6.5	1000	2700	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
Plug	G24d	10.5	92993	LED11G24d-H/830	#	6	6.5	1050	3000	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
In	G24d	10.5	92990	LED11G24d-H/835	#	6	6.5	1050	3500	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	G24d	10.5	92992	LED11G24d-H/840	#	6	6.5	1050	4000	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	VERTICAL 2-PIN														
Plug In	G24d	10.5	93002	LED11G24d-V/827	#	6	6.5	1000	2700	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	G24d	10.5	92988	LED11G24d-V/835	#	6	6.1	1050	3500	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed
	G24d	10.5	92996	LED11G24d-V/840	#	6	6.1	1050	4000	80	18 or 26	50,000	-	Damp	Magnetic Ballast, Fully Enclosed

- Check compatibility at gecurrent.com/LED2pin-compatibility



Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

- The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)
 ** Minimum order quantity = 6
 # UL 1993 Environmental Requirements for LED LAMPS
 Location, damp Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.
 Location, damp Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.
 Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to
 prevent an accumulation of moisture.
 Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.



www.gecurrent.com

© 2021 Current Lighting Solutions, LLC. All rights reserved. GE and the GE monogram are trademarks of the General Electric Company and are used under license. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. LEDL044 (Rev 03/11/21)