2400 Boston Street |Suite 200 | Baltimore, MD | 21224

# DAP<sup>®</sup> DYNAFLEX 230<sup>®</sup> Premium Elastomeric Sealant

#### **PRODUCT DESCRIPTION**

**DAP**<sup>®</sup> **DYNAFLEX 230**<sup>®</sup> is a premium elastomeric latex sealant with silicone-like toughness. It combines outstanding durability, adhesion and flexibility with easy tooling, paintability, low odor & water clean-up. It is highly flexible to handle joint movement caused by variations in temperature and humidity without cracking. It provides a long-lasting, durable seal that is 100% waterproof and weatherproof. Ideal for sealing air leaks around windows, doors, siding, trim and baseboards to improve the energy efficiency of a home and reduce utility costs. Cured sealant is mold and mildew resistant. Lifetime Guarantee. Meets ASTM Specification C920, Class 25. VOC compliant. Interior/exterior use.



PACKAGING	COLOR	UPC
10.1 fl oz (300 mL) Cartridge	White	7079818300
10.1 fl oz (300 mL) Cartridge	Almond	7079818306
10.1 fl oz (300 mL) Cartridge	Clay	7079818416
10.1 fl oz (300 mL) Cartridge	Cedar Tan	7079818412
10.1 fl oz (300 mL) Cartridge	Brown	7079818302
10.1 fl oz (300 mL) Cartridge	Gray	7079818301
10.1 fl oz (300 mL) Cartridge	Dark Bronze	7079818303
10.1 fl oz (300 mL) Cartridge	Black	7079818280
5.5 fl oz (162 mL) Tube	White	7079818285

2400 Boston Street |Suite 200 | Baltimore, MD | 21224

### **KEY FEATURES & BENEFITS**

- Silicone tough with superior flexibility & crackproof performance
- Seals joints up to 2" wide
- 100% waterproof & weatherproof seal
- Paintable in 2 hours
- Easy water clean-up
- Low odor
- Ideal for composite wood & PVC trimboard
- Meets ASTM C920, Class 25
- VOC compliant
- Lifetime Guarantee
- Interior/exterior use

#### SUGGESTED USES

#### **USE FOR CAULKING & SEALING:**

- Windows
- Doors
- Siding
- Trim
- Molding
- Pipes

#### ADHERES TO:

- Wood painted & unpainted
- Aluminum
- Most metals
- Vinyl
- Most plastics
- Plaster
- Drywall
- Glass

- Vents
- Corner Joints
- Butt Joints
- Tuck Pointing
- Other gaps & cracks
- Fiber Cement
- Stucco
- Composite
- PVC trimboard
- Brick
- Stone
- Concrete
- Mortar
- Most common building materials

2400 Boston Street |Suite 200 | Baltimore, MD | 21224

### FOR BEST RESULTS

- Apply in temperatures above 40°F.
- Do not apply when rain or freezing temperatures are forecasted within 24 hours. Cooler temperatures and higher humidity will slow down dry time.
- Not for continuous underwater use or filling surface defects.
- Joint size should not exceed 2" wide x 1/2" deep. If joint depth exceeds 1/2", use backer rod material.
- Store sealant away from extreme heat or cold.

### APPLICATION

#### Surface Preparation

Surface must be clean, dry, structurally sound and free of all old caulk, dirt and other foreign material.

#### Product Application

- 1. Apply in temperatures above 40°F. Do not apply when rain or freezing temperatures are forecasted within 24 hours. Cooler temperatures and higher humidity will slow down dry time.
- 2. If using the squeeze tube, remove cap.
- 3. Cut nozzle at 45° angle to desired bead size.
- 4. If using the cartridge, load into caulk gun.
- 5. Fill gap or joint with sealant.
- 6. If necessary, tool or smooth the bead of sealant with a finishing tool before sealant skins over.
- 7. Clean up excess wet sealant with a damp sponge before it skins over. Excess dried sealant must be cut or scraped away.
- 8. Allow sealant to dry 2-4 hours (longer in cool or humid conditions) before painting with latex or oil-based paints.
- 9. Reseal container for storage and reuse.

### TYPICAL PHYSICAL & CHEMICAL PROPERTIES

Typical Uncured Physical Properties	
Appearance/Consistency	Gunnable, non-sag paste
Base Polymer	Advanced acrylic polymer
Filler	Calcium carbonate
Volatile	Water
Weight % Solids	78%
Density (lbs per gallon)	12
Odor	Very mild

2400 Boston Street |Suite 200 | Baltimore, MD | 21224

Clean Up	Water		
Flash Point	>212°F		
Freeze Thaw Stability (ASTM C1183)	Passes 5 cycles		
Shelf Life	12 months		
Coverage	10.1 fl oz cartridge: 55 linear ft. at a 3/16" bead size		
	5.5 fl oz squeeze tube: 30 linear ft. at a 3/16" bead size		
Typical Application Properties			
Application Temperature Range	40°F to 100°F		
Tooling Time (Working Time)	10 minutes		
Tack Free Time	30 minutes		
Full Dry Through	24 hours		
Return to Service Time	24 hours		
Vertical Sag (ASTM D2202)	0.05"		
Typical Cured Performance Properties			
Service Temperature Range	-30°F to 180°F		
Water Ready Time	24 hours		
Paint Ready Time	2 hours		
Mildew Resistance	Cured caulk is mold & mildew resistant		
Dynamic Joint Movement (ASTM C719)	+/-25%		

### **CLEAN UP & STORAGE**

Clean up excess wet caulk with a damp sponge before it skins over. Excess dried caulk must be cut or scraped away. Clean hands and tools with warm water and soap. Store container in a cool, dry place away from extreme heat or cold.

### SAFETY

See product label or Safety Data Sheet (SDS) for health and safety information. You can request a SDS sheet by visiting our website at dap.com or calling 888-DAP-TIPS.

2400 Boston Street |Suite 200 | Baltimore, MD | 21224

### WARRANTY

**LIFETIME GUARANTEE:** DAP warrants this product for sealant purposes during the lifetime of your home, when used as directed, within one year of purchase. Call (888) DAP TIPS, with your sales receipt and product container available for replacement product or sales price refund. DAP is not liable for incidental or consequential damages.

### COMPANY IDENTIFICATION

Manufacturer: DAP Products Inc., 2400 Boston Street, Baltimore, Maryland 21224

Usage Information: Call 888-DAP-TIPS or visit dap.com & click on "Ask the Expert"

Order Information: 800-327-3339 or orders@dap.com

Fax Number: 410-558-1068

Also, visit the DAP website at dap.com