

# Product data sheet

## Characteristics

# 8903SPO2V02

Contactor, Type S, multipole lighting, electrically held, 60A, 3 pole, 110/120 VAC 50/60 Hz coil, open style



### Main

Product	Electrically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	60 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	5.51 in (140 mm)
Depth	4.92 in (125 mm)
Width	4.33 in (110 mm)

### Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed CSA

### Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	785901619451
Nbr. of units in pkg.	1
Package weight(Lbs)	5.63 lb(US) (2.554 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.00 in (17.78 cm)
Package 1 width	6.50 in (16.51 cm)
Package 1 Length	9.40 in (23.876 cm)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------