


REV	DESCRIPTION	ECN#	CHG BY	DATE	APP'D
Α	CONVERTED TO 3D	WEB	NAS	09/30/19	NAD







ELEMENT SPECS			
PART NUMBER	PART NUMBER 32-19		
MATERIAL	POLYESTER		
FLOW RATE	N/A	N/A	
SURFACE AREA	5.8 ft <sup>2</sup>	0.5 m <sup>2</sup>	
I.D.	7.10"	180mm	
O.D.	10.15"	258mm	
HEIGHT	5.13"	130mm	



THE INFORMATION CONTAINED HEREIN IS CONFIDENTIAL AND THE PROPERTY OF SOLBERG MANUFACTURING INC. AND IT IS FURNISHED TO YOU WITH THE EXPRESS UNDERSTANDING THAT IT WILL NOT BE REPRODUCED, COPIED IN ANY MANNER, LOANED OR OTHERWISE TRANSFERRED TO OTHERS ENTIRELY OR IN PART, NOR USED FOR ANY PURPOSE OTHER THAN FOR WHICH IT WAS ELIBBILED IN DON DECLIFICATION. WAS FURNISHED. IT WILL BE RETURNED UPON REQUEST TO SOLBERG MANUFACTURING INC. THE ABOVE RESTRICTION IS IN ADDITION TO, AND DOES NOT IN ANY WAY ALTER, ANY OTHER RESTRICTIONS WHICH MAY APPLY TO THE INFORMATION CONTAINED HEREIN.

## **TOLERANCES**

DIMENSIONS ARE FOR REFERENCE ONLY. ALL DIMENSIONS ARE SUBJECT TO CHANGE **UPON PRODUCTION.** 

UNLESS OTHERWISE SPECIFIED:
-DIMENSIONS ARE IN INCHES
-REF: APPROXIMATE DIMENSIONS, NO TOLERANCES APPLY
-FINISH: BREAK EDGES TO .005-.020 RADIUS/CHAMFER

MODEL NUMBER: 32-19	SHEET:
WODEL NOMBER. 52-15	1 OF 1

**DESCRIPTION:** 32-19, POLY

	PROJECT:	DRAWN BY: CMA	APPROVED BY: M.C.	REV:
	SD15908	<b>DATE</b> : 8/11/2010	<b>DATE</b> : 8/11/2010	Α