

# FISSURED™

Square Lay-in & Tegalular  
medium texture

Declare.  
**GREENGUARD**  
Gold Certified  
(details below)

LEED® WELL™ LBC  
UP TO **41%** RECYCLED CONTENT

energy management  
construction waste mgmt  
regional materials  
design for flexibility  
EPD  
recyclable/producer resp.  
biobased materials  
recycled content  
sourcing of raw materials  
material ingredient reporting  
low emitting materials  
lighting quality  
acoustics

Calculate sustainability with GreenGenie™  
armstrongceilings.com/greengenie

LOCATION DEPENDENT



▲ Fissured™ Angled Tegalular panels with Prelude® XL® 15/16" suspension system

Economical panels; Directional with standard acoustical performance. \$\$\$\$

### KEY SELECTION ATTRIBUTES

- Economical
- Directional fissured image

### COLOR



### VISUAL SELECTION

### PERFORMANCE SELECTION


Dots represent high level of performance.

armstrongceilings.com/catdwgs	Susp. Dwg.	Item No.	Dimensions (Inches)		UL Classified Acoustics NRC + CAC =	Total Acoustics <sup>1</sup>	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	Durability	Recycled Content	Recycle Program	Warranty	
			Width	Length												
FISSURED™ Square Lay-in 15/16" Square Lay-in	1	756	24 x 24	5/8"	0.55	30	N/A	Class A	0.79	N/A	Std	•	Std	Std	•	1-Yr
		896	24 x 24	5/8"	0.55	35	N/A	Fire Guard™	0.79	N/A	Std	•	Std	Std	•	1-Yr
		755	24 x 48	5/8"	0.55	30	N/A	Class A	0.79	N/A	Std	•	Std	Std	•	1-Yr
		895	24 x 48	5/8"	0.55	35	N/A	Fire Guard™	0.79	N/A	Std	•	Std	Std	•	1-Yr
FISSURED™ Tegalular 15/16" Angled Tegalular	12	705	24 x 24	5/8"	0.55	30	N/A	Class A	0.79	N/A	Std	•	Std	Std	•	1-Yr
		815	24 x 24	5/8"	0.55	35	N/A	Fire Guard™	0.79	N/A	Std	•	Std	Std	•	1-Yr
Made-to-Order Sizes			5/8" Thick – 15/16" Square Lay-in & Tegalular		N/A	N/A	Class A	0.79	N/A	Std	•	Std	Std	•	1-Yr	
			Width	Length												
			12" - 30"	18" - 72"												

**4-6 WEEKS**  
order to ship

<sup>1</sup> Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.

### SUSPENSION SYSTEMS



### PHYSICAL DATA

**Material**  
Wet-formed mineral fiber

**Surface Finish**  
Factory-applied latex paint

**Fire Performance**  
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

Fire Guard™: A fire-resistive ceiling when used in applicable UL assemblies

**ASTM E1264 Classification**  
Type III, Form 2, Pattern C D  
Fire Class A

**Humidity/Sag Resistance**  
Standard performance ceiling panels are recommended where the building is enclosed and the HVAC is continuously functioning.

**VOC Emissions**  
**GREENGUARD Gold Certified**  
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS  
UL.COM/GG  
UL 2818



**Insulation Value**  
755, 756, 895, 896 – R Factor – 1.5 (BTU units)  
R Factor – 0.26 (Watts units)  
705, 815 – R Factor – 1.6 (BTU units)  
R Factor – 0.28 (Watts units)

**1-Year Limited Warranty**  
Details at armstrongceilings.com/warranty

**Weight; Square Feet/Carton**  
705 – 0.69 lbs/SF; 64 SF/ctn 815 – 1.08 lbs/SF; 48 SF/ctn  
755 – 0.66 lbs/SF; 96 SF/ctn 895, 896 – 1.09 lbs/SF;  
756 – 0.67 lbs/SF; 64 SF/ctn 64 SF/ctn

**Minimum Order Quantity**  
1 carton, excludes made-to-order panels

**Metric Items Available**  
756M, 896M, 755M, 895M, 705M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.

