

Miller Positioning & Restraint Lanyards (for Wind Industry)

Models: 1014936, 1014937

Description

Rope lanyards recommended for work positioning or restraint ONLY.

Materials

Rope: Kernmantle

- 1014936: 1/2 inch rope
- 1014937: 5/8 inch rope

Hardware: Steel

- Twist-Lock Carabiners: 1 in. (25mm) gate opening
- Locking Rebar Hooks: 2 1/2 in. (63mm) gate opening

* All hardware meets ASTM (50) fifty-hour salt spray test requirements.

Label Materials: Valeron

Technical

Max. Working Load: 310 lbs (141 kg)

Min. Tensile Strength/Gate Strength

- **Rope:** 5,000 lbs. (22kN)
Tensile Strength on rope
- **Rope Grab:** 3,600lbs (16kN) Tensile Strength
- **Snap Hook:** 5,000lbs (22.2kN) Tensile Strength
3,600 lb. (16kN) Gate Strength
- **Carabiner:** 5,000lbs (22.2kN) Tensile Strength
3,600 lb. (16kN) Gate Strength

Certification

OSHA 1926.502, 1910.66; ANSI A10.32, Z359.3,
CSA Z259.11, EN354 (1014936), EN358 (1014937)



Model #	Length	Description
1014936	4 ft. (1.2m)	Restraint Lanyard w/Locking Rebar hook and Twist-Lock Carabiner
1014937	6 ft. (1.8m)	Adjustable Positioning Lanyard w/Locking Rebar hook and a non-removable adjustable rope grab with captive-eye carabiner

MILLER®

by Honeywell

Toll Free 800.873.5242 (press 4) • hsptechsupport@honeywell.com • www.millerfallprotection.com

⚠ WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.