


Explosion Proof LED Floodlight

The new XP970LED is revolutionizing hazardous location lighting by combining high light output and durability in a product that's a fraction of the traditional cost. There is no other product like it on the market. The bright, portable and heavy-duty XP970LED is a new and improved explosion proof light with a high-powered LED within. The light comes standard with a 50' cord and a non- XP plug. Explosion proof plugs and 100' cord lengths are available. Additionally, replacement parts are easily available to maintain durability in your lights.

Approvals:

cULus Certified for Class I, Division 1, Groups B, C and D.
Class II, Division 1, Groups E, F and G



XP970LED

XP970LED-FS

5660 lumen Explosion-Proof LED Floodlight w/50' cord and floor stand

XP970LED-MAG

5660 lumen Explosion-Proof LED Floodlight w/50' cord and magnet mount

XP970LED-TR

5660 lumen Explosion-Proof LED Floodlight w/50' cord and 4-8' tripod

XP970LED-TD

2 x 5660 lumen Explosion-Proof LED Floodlights w/50' and 4-8' tripod



XP970LED-FS



XP970LED-TD

KEY FEATURES

- Easily portable.
- LEDs will last over 50,000 hours.
- No bulb replacement required.
- Instant start-up, at full output, even in cold temperatures.
- Rugged heavy duty frame

KEY BENEFITS

- Safer working environment.
- Lower total cost of ownership.
- Reduced downtime on job sites.
- Energy saving device for a greener footprint.

SPECIFICATIONS

SPECIFICATIONS	
VOLTAGE	90 - 277V AC
WATTAGE	40W (0.33A @ 120V)
LIGHT TEMPERATURE	4500K (bright white light • no
LUMENS	5,660 lumens
LIGHT EXPECTANCY	Rated for over 50,000 hours
CONSTRUCTION	Cast aluminum housing with tempered glass lens
DIMENSIONS	3.75"D x 11"H x 12.5"W
WEIGHT	17 lbs (less cable)

