


Explosion Proof LED Floodlight

Brighter and more powerful than the XP970LED, this explosion proof floodlight has all the benefits of the smaller model, with more power. Standard models include a 16/3 SOOW cord and non-xp plug. The XP980LED comes with standard with a 50' cord and a non-XP plug Explosion Proof plugs and 100' cord length available.



Approvals:

cULus Certified for Class I, Division 1, Groups B, C and D. Class II, Division 1,

SKUs

XP980LED-FS

24,000 lumen Explosion-Proof LED Floodlight w/50' cord and floor stand

XP980LED-TR

24,000 lumen Explosion-Proof LED Floodlight w/50' cord and 4-8' heavy-duty tripod

KEY FEATURES

- Easily portable.
- LEDs will last over 50,000 hours.
- No bulb replacement required.
- Instant start-up, at full output, even in cold temperatures.
- Rugged heavy duty frame

KEY BENEFITS

- Safer working environment.
- Lower total cost of ownership.
- Reduced downtime on job sites.
- Energy saving device for a greener footprint.

SPECIFICATIONS

SPECIFICATIONS	
VOLTAGE	90 - 277V AC
WATTAGE	160W (1.33A @ 120V)
LIGHT TEMPERATURE	4500K (bright white light • no blue tint)
LUMENS	24,000 lumens
LIGHT EXPECTANCY	Rated for over 50,000 hours
CONSTRUCTION	Cast aluminum housing with tempered glass lens
DIMENSIONS	3.75"D x 14"H x 15.5"W
WEIGHT	35 lbs (less cable)

