

NEW



M12 FUEL™

DRIVEN TO OUTPERFORM.™



**MOST
POWERFUL**
SUBCOMPACT
HAMMER DRILL

FASTEST
SUBCOMPACT
IMPACT DRIVER

**MOST
COMPACT**

**M12 FUEL™ 2-Tool Combo Kit:
1/2" Hammer Drill/Driver and
1/4" Hex Impact Driver**

3497-22 / 794JK2

REDLITHIUM™
CP2.0/XC4.0



DRIVEN TO OUTPERFORM.™

M12 FUEL™ is engineered for the most demanding tradesmen in the world. M12 FUEL™ delivers unrivaled performance in a compact structure and features three MILWAUKEE® exclusive innovations — the POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software — that deliver unmatched power, run-time and durability. Simply put, the M12 FUEL™ 1/2" Hammer Drill/Driver and the M12 FUEL™ 1/4" Hex Impact Driver are the industry's best sub compact drill and impact driver.

M12 FUEL™

1 POWERSTATE™ BRUSHLESS MOTOR

- MILWAUKEE® Designed and Built Brushless Motor
- Outperforms All Leading Competitors


2 REDLINK PLUS™ INTELLIGENCE

- Most Advanced Electronic System on the Market for Maximum Performance
- Total System Communication with Overload Protection Increases Tool Life
- Built-in Fuel Gauge Displays Remaining Charge


3 REDLITHIUM™ CP2.0 & XC4.0 BATTERY PACKS

- Up to 2X Run-Time
- Up to 2X More Recharges than Leading Competitor
- Operates Below -18°C / 0°F

MOST POWERFUL SUBCOMPACT HAMMER DRILL



FASTEST SUBCOMPACT IMPACT DRIVER



MOST COMPACT



POWERSTATE™ BRUSHLESS MOTOR

All-new motor design and innovative motor control for faster app speed while being the most powerful drill in its class

MECHANICAL DESIGN

New M-clutch design for wider range of torque settings and improved fastening performance

ALL-METAL CHUCK

Improved bit retention and increased durability

LED WORKLIGHT

Illuminates the work surface

VARIABLE SPEED TRIGGER

Enhanced application control

BATTERY GAUGE

Run-time indication

TRI-LED WORKLIGHTS

Maximum workspace visibility

4-SPEED DRIVE CONTROL™

Adjust impact driver speed for increased performance and control. Also featuring self-tapping screw mode

POWERSTATE™ BRUSHLESS MOTOR

All-new motor design for fastest subcompact impact driver

SINGLE HANDED BIT INSERTION

One-handed acceptance for ease of use

VARIABLE TRIGGER SPEED

Enhanced application control

PREMIUM RUBBER OVERMOLD

Increased comfort for all-day use



SPECIFICATIONS AND MODELS

DESCRIPTION		3404 SPECIFICATIONS		DESCRIPTION		3453 SPECIFICATIONS	
RPM		0 – 1,550		Anvil Type		1/4" Hex Driver	
BPM		22,500		Peak Torque		1,500 in-lbs	
Torque		400 in-lbs		RPM		1,500 / 2,700 / 3,600 / 0 – 3,600	
Chuck		1/2" All-Metal Chuck		IPM		0 – 4,000	
Length		6"		DRIVE CONTROL™		4-Mode	
Weight (w/ CP2.0 Battery)		2.6 lbs		Single Handed Bit Insertion		Yes	
Weight (w/ XC4.0 Battery)		3.1 lbs		Tri-LED		Yes	
				Length		5"	
				Weight (Tool-Only)		1.6 lbs	



M12 FUEL™ 2-Tool Combo Kit
3497-22 / 794JK2

Includes: 3404-20 1/2" Hammer Drill/Driver, 3453-20 1/4" Hex Impact Driver, (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, M12™ Charger, (2) Belt Clips and Contractor Bag.





FUEL FUEL FUEL FUEL FUEL FUEL SURGE FUEL FUEL FUEL FUEL FUEL FUEL



FUEL FUEL FUEL FUEL FUEL FUEL FUEL FUEL FUEL FUEL FUEL



M12

**PORTABLE PRODUCTIVITY
TRADE FOCUSED
SYSTEM WIDE**



M12 FUEL™ 2-Tool Combo Kit
M122-5645

milwaukeetool.com

©2022 Milwaukee® Tool