

99 11 300

High Leverage Concretors' Nipper high lever transmission



- for fixing Monier iron in place with tie wire from a roll
- Wire is twisted and cut in a single pass.
- high-leverage joint, minimising strain, even when thick binding wires are used
- very slim shape for tying submerged positioned steel rods
- The high damping of the cutting stroke on cutting through the tie wire reduces the strain on tendons and muscles.
- Cutting edges with additional hardness; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, oil-hardened

compared to conventional concretors' nippers of the same size.

Product Number	99 11 300
EAN	4003773042365
Pliers	black atramentized
Head	polished
Handles	plastic coated
hard wire Ø mm	2
medium hard wire Ø mm	3,8
Head width mm	25
Length mm	300
Net weight g	537



technical change and errors excepted

