

CU THERMOSTAT CABLE

Sunlight-Resistant 60°C.150 volts
18 and 20 Gauge Copper Conductors.



Construction

Southwire Thermostat Wire is manufactured using solid copper conductors with 6 mils of polyvinyl chloride insulation. The two conductor cable is flat - multiconductor cables are round.

Applications

Southwire's Thermostat Wire is a class 2 power-limited circuit cable for use in heating and air conditioning controls (bell and alarm systems).



Specifications

- CL2- Power Limited per NEC Article 725. MP- Multi Purpose Cable per Articles 725, 760, and 800.
- CM-Communication Cable per Article 800
- FPL - Power Limited Fire Protective Signaling Cable per Article 760
- Sunlight Resistant, PVC Insulation, and Solid Bare Copper per UL Standard 13
- RoHS Compliant
- OSHA Acceptable



greenSpec

RoHS Compliant



MADE IN AMERICA



INDOOR WIRE

| Size (AWG) | Conductor | | Jacket Thickness (mils) | Ground Wire | | Cable Dimension (mils) | Approx. Weight per 1000' (lbs) | Allowable Ampacity | Standard Package |
|------------|-------------------|--|-------------------------|-------------|-------------------|------------------------|--------------------------------|--------------------|------------------|
| | Number of Strands | Insulation and Jacket Thickness (mils) | | Size (AWG) | Number of Strands | | | | |
| 18 | | | - | | | - | | - | |
| 18 | | | - | | | - | | - | |
| 20 | | | - | | | - | | - | |