




**NOTES:**

- 1. HIGH PURITY: 200 K Ohms SETPOINT LIGHT
- 2. HIGH CAPACITY: 50 K Ohms SET POINT LIGHT
- 3. MAX PRESSURE: 100 PSI
- 4. MAX TEMP: 100 F°

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED



	DRAWN KMC	DATE 12/12/12	<b>HYDRA-122B-DI</b>  <b>DEIONIZED WATER SYSTEM</b>			
	CHECKED JB	12/12/12				
	QA HRD	12/12/12	SIZE <b>A</b>	FSCM NO.	DWG NO. <b>S-HY-122B-DI</b>	REV <b>A</b>
Materials: N/A	MFG KMC	12/12/12	SCALE N/A		SHEET 1 OF 1	
Finish: N/A	APPROVED FF	12/12/12				