

# Masterflow<sup>®</sup> Heat Blower

Professional quality, continuous-duty, process heat blower




Replacement Heating Element

\* NEMA 5-20P Plug

- 3 models produce 300°F, 500°F or 750°F. High temperatures accommodate many heating, drying & shrinking applications
- High air flow: 47 CFM at 2200 FPM gets job done fast
- Brushless induction type motor for quiet, continuous-duty operation
- Easily replaceable, reinforced, mica-insulated heating element
- Rubber-backed stand permits 90° non-slip adjustability
- Use in any position or mount on equipment
- Ergonomic handle for carrying or portable use
- Mount over conveyor line or on machinery
- Use to heat or dry materials, bend plastics, shrink wrap and more

## Specifications

- Air Volume: 47 CFM ■ Air Velocity: 2200 FPM ■ Motor: Induction ■ Nozzle Opening: 1.85" I.D., 2.25" O.D.
- Dimensions: 12" L x 6" W x 9" H, (AH-301 & AH-302, 9" L x 6" W x 9" H) ■ Base Size: 6" x 6" ■ Cordset: 6 ft., 3-wire grounded ■  ■ Net Weight: 6 lbs. ■ Shipping Weight: 8 lbs.

MODEL NO.	DESCRIPTION	REPLACEMENT ELEMENT
AH-301	300°F 150°C 120V 10.0A 60 Hz 1200W	815
AH-501	500°F 260°C 120V 14.0A 60 Hz 1680W	30310
AH-751 *	750°F 400°C 120V 18.0A 60 Hz 2160W	30312
AH-302	300°F 150°C 240V 5.2A 60 Hz 1200W	816
AH-502	500°F 260°C 240V 7.3A 60 Hz 1680W	30311
AH-752	750°F 400°C 240V 9.4A 60 Hz 2160W	30313

NOTE: Users should independently evaluate the suitability of the product for their application.