


ADD-A-LEVEL™ ALL-PLASTIC WORK PLATFORMS



| Add-A-Level™ 2-5/8" Thick Platforms | | | |
|--|--------|----------------------|-----|
| Sizes | Part # | Desc. | Wt. |
| 36"x 16" | A3616B | 36"x 16" Base Unit | 9 |
| | A3616A | 36"x 16" Add-on Unit | 9 |
| 66"x 16" | A6616B | 66"x 16" Base Unit | 16 |
| | A6616A | 66"x 16" Add-on Unit | 16 |
| 96"x 16" | A9616B | 96"x 16" Base Unit | 21 |
| | A9616A | 96"x 16" Add-on Unit | 21 |
| 36"x 24" | A3624B | 36"x 24" Base Unit | 12 |
| | A3624A | 36"x 24" Add-on Unit | 12 |
| 48"x 24" | A4824B | 48"x 24" Base Unit | 15 |
| | A4824A | 48"x 24" Add-on Unit | 15 |
| 66"x 24" | A6624B | 66"x 24" Base Unit | 20 |
| | A6624A | 66"x 24" Add-on Unit | 19 |
| 96"x 24" | A9624B | 96"x 24" Base Unit | 30 |
| | A9624A | 96"x 24" Add-on Unit | 29 |
| 36"x 36" | A3636B | 36"x 36" Base Unit | 18 |
| | A3636A | 36"x 36" Add-on Unit | 18 |
| 66"x 36" | A6636B | 66"x 36" Base Unit | 31 |
| | A6636A | 66"x 36" Add-on Unit | 31 |
| 96"x 36" | A9636B | 96"x 36" Base Unit | 45 |
| | A9636A | 96"x 36" Add-on Unit | 44 |


| Accessories | |
|-------------|--|
| Part # | Desc. |
| R1102 | 2'L x 10"W x 2-5/8"H Wooden Ramp |
| R1103 | 3'L x 10"W x 2-5/8"H Wooden Ramp |
| R1104 | 4'L x 10"W x 2-5/8"H Wooden Ramp |
| R110C | 2-5/8" H Corner Wooden Ramp |
| CA2002 | Stacker (for vertical stacking) |
| RC3000 | Poly-Clip (for horizontal connections) |
| RF2011 | Rubber foot (included in base units) |
| MPL004 | Mat Plug Lock (included in matting) |

- **Build out horizontally and up vertically**
- **Easy no-tool installation**
- **Chemical-resistant plastic components**

Our modular, stackable work platforms create the perfect working height for your operations. Add-A-Level™ is easily assembled without tools and can stack horizontally to fill a floor, or vertically to give your employees a lift! Made from heavy-duty molded plastic components, geared toward ergonomics, designed to accommodate the 250 pound individual, they are a perfect fit in the harshest manufacturing environment.

Add our 1/2" or 7/8" thick comfort matting and you'll see an instant payoff in fewer fatigue related injuries along with dramatically increased productivity. Add-A-Level™ also makes an ideal decontamination platform because it allows water and chemical contaminants to flow through.

Capacity = 250 lbs per
30" Workstation Area



Plan View

Matting

| Sizes | 1/2" Matting | | | 7/8" Matting | | |
|----------|--------------|---------------|-----|--------------|---------------|-----|
| | Part # | Style | Wt. | Part # | Style | Wt. |
| 36"x 24" | M23120 | Black Mat | 10 | M23780 | Black Mat | 17 |
| | M23125 | Yellow Border | 12 | M23784 | Yellow Border | 17 |
| 48"x 24" | M24120 | Black Mat | 13 | M24780 | Black Mat | 22 |
| | M24125 | Yellow Border | 15 | M24784 | Yellow Border | 22 |
| 66"x 24" | M25120 | Black Mat | 16 | M25780 | Black Mat | 29 |
| | M25125 | Yellow Border | 19 | M25784 | Yellow Border | 29 |
| 96"x 24" | M28120 | Black Mat | 26 | M28780 | Black Mat | 44 |
| | M28125 | Yellow Border | 28 | M28784 | Yellow Border | 44 |
| 36"x 36" | M33120 | Black Mat | 15 | M33780 | Black Mat | 25 |
| | M33125 | Yellow Border | 17 | M33784 | Yellow Border | 28 |
| 66"x 36" | M35120 | Black Mat | 25 | M35780 | Black Mat | 46 |
| | M35125 | Yellow Border | 27 | M35784 | Yellow Border | 50 |
| 96"x 36" | M38120 | Black Mat | 35 | M38780 | Black Mat | 66 |
| | M38125 | Yellow Border | 39 | M38784 | Yellow Border | 72 |