


**DUNE™**  
 Square Lay-in & Tegular  
 fine texture



CAD/Revit® drawings at:  
[armstrongceilings.com/cadrevit](http://armstrongceilings.com/cadrevit)



▲ Dune™ Square Lay-in panels with Prelude® XL® 15/16" suspension system

▲ Dune Tegular panels with Interlude® XL HRC 9/16" suspension system

Fine-textured panels are non-directional and durable with standard acoustical performance.

**KEY SELECTION ATTRIBUTES**

- new** • Dune™ panels are part of the Sustain® portfolio, and meet the most stringent industry sustainability compliance standards today
- Upgrade look at a modest price
- Ceiling-2-Ceiling™ Post-consumer Recycled Content options: Items 1773HRC, 1774HRC, 1775HRC, 1776HRC, 1777HRC (check [armstrongceilings.com/greengenie](http://armstrongceilings.com/greengenie))

- Mold- and mildew-resistant surface
- USDA-Certified Biobased Product – 99%
- Durable – Scratch-resistant
- Non-directional visual reduces scrap and installation time
- Product can be recycled through the

- Armstrong Ceilings Recycling Program
- 30-Year Limited System Warranty against visible sag (excludes items 1796 and 1798), mold and mildew
  - 10-Year replacement panel available for items 1772, 1773, 1774, 1775, 1776



**COLOR**



White  
 (WH)

**DETAILS** (Other Suspension Systems compatible. Refer to listing on next page.)



1. Dune™ Tegular
2. Dune™ Square Lay-in with Prelude® 15/16" suspension system
3. Dune™ Tegular with Suprafine® 9/16" suspension system
4. Dune™ Tegular with Silhouette® XL® 9/16" suspension system with 1/4" reveal
5. Dune™ Tegular with Interlude® XL® HRC 9/16" suspension system

# DUNE™

Square Lay-in & Tegalur  
fine texture



USDA  
CERTIFIED  
BIOBASED  
PRODUCT  
PRODUCT 99%

Declare.

SUSTAIN™  
High Performance  
Sustainable Ceiling Systems

GREENGUARD  
Gold Certified  
(details below)

LEED®  
WELL™ LBC

UP TO 56% RECYCLED CONTENT

- energy management
- construction waste mgmt
- regional materials
- design for flexibility
- EPD
- recyclable/producer resp.
- biobased materials
- recycled content
- sourcing of raw materials
- material ingredient reporting
- low emitting materials
- lighting quality
- acoustics

Calculate sustainability with GreenGenie™  
armstrongceilings.com/greengenie

LOCATION DEPENDENT

## VISUAL SELECTION

armstrongceilings.com/catdws	Susp. Dwg.	Item No.	Dimensions (Inches)
DUNE™ 15/16" Square Lay-in 	1	1772	24 x 24 x 5/8"
		1850	24 x 24 x 5/8"
		1773 1773HRC	24 x 48 x 5/8"
		1851	24 x 48 x 5/8"
		1796	20 x 60 x 3/4"
		1798	30 x 30 x 3/4"
3/4" or 5/8" Thick – 15/16" Square Lay-in			
Made-to-Order Sizes		Width	Length
		12" - 30"	18" - 72"

4-6 WEEKS order to ship

## PERFORMANCE SELECTION

Dots represent high level of performance.


\$\$\$\$

UL Classified Acoustics	Total Acoustics <sup>1</sup>	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	DURABILITY	Recycled Content	Recycle Program	30-Yr Warranty
NRC + CAC =							Scratch			
0.50 30	N/A	Class A	0.81	•	•	•	•	Std	•	•
0.50 35	N/A	Fire Guard™	0.81	•	•	•	•	Std	•	•
0.50 30	N/A	Class A	0.81	•	•	•	•	Std	•	•
0.50 35	N/A	Fire Guard	0.81	•	•	•	•	Std	•	•
0.50 35	N/A	Class A	0.81	•	Std	•	•	•	•	1-Yr
0.50 35	N/A	Class A	0.81	•	Std	•	•	•	•	1-Yr
N/A	N/A	Class A	0.81	•	Std	•	•	Std	•	1-Yr

<sup>1</sup> Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.

MORE ITEMS ►

## SUSPENSION SYSTEMS



## PHYSICAL DATA

**Material**  
Wet-formed mineral fiber

**Surface Finish**  
Factory-applied latex paint

**Fire Performance**  
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).  
Fire Guard™: A fire-resistive ceiling when used in applicable UL assemblies.

**ASTM E1264 Classification**  
Type III, Form 2, Pattern C E  
Fire Class A

**Humidity/Sag Resistance**  
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications. Excludes large made-to-order panels.

**Anti-Mold/Mildew**  
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

**Acoustical Performance**  
CAC testing conducted using Prelude® suspension system.

**VOC Emissions**  
GREENGUARD Gold Certified  
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

**Primary (Embodied) Energy**  
See all LCA information on our EPDs.

**High Recycled Content**  
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines. HRC items contain 15% or greater post-consumer recycled ceilings.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS  
UL.COM/GG  
UL 2818



**Insulation Value**  
R Factor – 1.6 (BTU units)  
R Factor – 0.28 (Watts units)

**30-Year Performance Guarantee & Warranty**  
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty (Excludes items 1796, 1798, and large other size panels)

**Weight; Square Feet/Carton**  
1772 – 0.94 lbs/SF; 64 SF/ctn  
1773 – 0.88 lbs/SF; 64 SF/ctn  
1796 – 1.33 lbs/SF; 67 SF/ctn  
1798 – 1.14 lbs/SF; 50 SF/ctn  
1850 – 1.19 lbs/SF; 48 SF/ctn  
1851 – 1.22 lbs/SF; 64 SF/ctn

**Minimum Order Quantity**  
1 carton

**Metric Items Available**  
1772M, 1850M, 1773M, 1851M, 1796M, 1798M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.

# DUNE™

Square Lay-in & Tegular  
fine texture



USDA  
CERTIFIED  
BIOBASED  
PRODUCT  
PRODUCT 99%

SUSTAIN™  
High Performance  
Sustainable Ceiling Systems

GREENGUARD  
Gold Certified  
(details below)

Declare.™

LEED® WELL™ LBC

UP TO 56% RECYCLED CONTENT

energy management  
construction waste mgmt  
regional materials  
design for flexibility  
EPD  
recyclable/extended producer resp.  
biobased materials  
recycled content  
sourcing of raw materials  
material ingredient reporting  
low emitting materials  
lighting quality  
acoustics

LOCATION DEPENDENT

Calculate sustainability with GreenGenie™  
armstrongceilings.com/greengenie

## VISUAL SELECTION

## PERFORMANCE SELECTION


Dots represent high level of performance.

armstrongceilings.com/catdws	Susp. Dwg.	Item No.	Dimensions (Inches)	UL Classified Acoustics		Total Acoustics <sup>1</sup>	Fire Performance	Light Reflect	Bio-Block Anti-Mold/ Mildew	Humi-Guard+ Sag Resistant	Certified Low VOC Emissions	DURABILITY Scratch	Recycled Content	Recycle Program	30-Yr Warranty
				NRC	CAC										
DUNE™ 15/16" Angled Tegular	12	1774	24 x 24 x 5/8"	0.50	35	N/A	Class A	0.81	•	•	•	•	Std	•	•
		1774HRC	24 x 24 x 5/8"	0.50	35	N/A	Fire Guard	0.81	•	•	•	•	Std	•	•
		1776	24 x 48 x 5/8"	0.50	35	N/A	Class A	0.81	•	•	•	•	Std	•	•
9/16" Beveled Tegular	29	1775	24 x 24 x 5/8"	0.50	35	N/A	Class A	0.81	•	•	•	•	Std	•	•
		1775HRC	24 x 24 x 5/8"	0.50	35	N/A	Fire Guard	0.81	•	•	•	•	Std	•	•
		1852	24 x 24 x 5/8"	0.50	35	N/A	Fire Guard	0.81	•	•	•	•	Std	•	•
3/4" or 5/8" Thick – 15/16" & 9/16" Angled Tegular	44	1777	24 x 48 x 5/8"	0.50	35	N/A	Class A	0.81	•	•	•	•	Std	•	•
		1777HRC	24 x 48 x 5/8"	0.50	35	N/A	Class A	0.81	•	•	•	•	Std	•	•
		1852	24 x 24 x 5/8"	0.50	35	N/A	Fire Guard	0.81	•	•	•	•	Std	•	•
Made-to-Order Sizes			Width	Length	N/A	N/A	N/A	Class A	0.81	•	Std	•	Std	•	1-Yr

4-6 WEEKS order to ship

<sup>1</sup> Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.

## SUSPENSION SYSTEMS



## PHYSICAL DATA

**Material**  
Wet-formed mineral fiber

**Surface Finish**  
Factory-applied latex paint

**Fire Performance**  
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).  
Fire Guard™: A fire-resistive ceiling when used in applicable UL assemblies (Class A)

**ASTM E1264 Classification**  
Type III, Form 2, Pattern C E  
Fire Class A

**Humidity/Sag Resistance**  
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications. Excludes large made-to-order panels.

**Anti-Mold/Mildew**  
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

**Acoustical Performance**  
CAC testing conducted using Prelude® suspension system.

**VOC Emissions**  
GREENGUARD Gold Certified  
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

**Primary (Embodied) Energy**  
See all LCA information on our EPDs.

**High Recycled Content**  
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines. HRC items contain 15% or greater post-consumer recycled ceilings.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS  
UL.COM/GG UL 2818



**Insulation Value**  
R Factor – 1.6 (BTU units)  
R Factor – 0.28 (Watts units)

**30-Year Performance Guarantee & Warranty**  
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty

**Weight; Square Feet/Carton**  
1774, 1774HRC, 1775, 1775HRC – 0.75 lbs/SF; 64 SF/ctn  
1776, 1776HRC, 1777, 1777HRC – 0.75 lbs/SF; 64 SF/ctn  
1852, 1853 – 1.20 lbs/SF; 48 SF/ctn

**Minimum Order Quantity**  
1 carton

**Metric Items Available**  
1775M, 1777M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.

MINERAL FIBER – Standard