



TOUGHSTRIPE[®]
Floor Marking

AVAILABLE THROUGH
GRAINGER[®]
FOR THE ONES WHO GET IT DONE



TOUGHSTRIPE® Floor Marking

Superior Durability

Spend less time replacing damaged or worn lines for a better-looking, more efficient facility.

- Withstands forklift traffic without tearing or lifting
- Low-profile design minimizes tears and scratches from skids, pallet jacks, etc.
- Rugged polyester with ultra-aggressive adhesive

Easy Application

Quickly lay down smooth, straight lines – without the help of coworkers.


- Can be easily applied by one person working alone
- Stiff polyester with liner prevents tape stretching and reduces wrinkles and wavy, uneven lines
- No special floor preparation required – just clean with common cleansers

* For maximum performance, apply ToughStripe Floor Marking products to flat, non-coated concrete.



ToughStripe® Floor Tape Adhesion Rates

Floor Types



Questions about your floor type?

We recommend testing a small area before purchasing.



High Visibility

Get the same visibility of painted floor markings – and pay less.

- High-gloss surface shines like new paint
- Low profile minimizes debris buildup along the edges that occurs with thicker (extruded) floor tapes
- Surface resists marks and smudges
- Available in a variety of high-impact colors
- Custom colors available



Diecut Shapes

Utilize different shapes, colors and sizes for more effective, durable floor markings.

- Dashes, dots, arrows, footprints, and corner marks (L, T and + shapes)
- Longer lasting markings – Minimizes the risk of damage and facilitates fast repair



Pre-Spaced Shapes

Expedite installation and repair time

- Dots, arrows and dashes packaged in rolls (not individually) and evenly spaced 18" apart on a continuous liner
- Quick and easy one person installation; simply lay down the line like a continuous tape, and then remove the clear transfer tape from on top of the floor markings
- Eliminates the need to apply markings one by one
- Quickly lay straight, evenly spaced shapes
- Ideal for high traffic areas – if damaged only replace damaged shapes

Use ToughStripe® Floor Marking products to mark:

- Aisleways and traffic lanes
- Work Cell outlines
- Equipment storage areas
- Material storage areas
- QA inspection areas
- Defects/scrap/rework areas
- "Keep clear" zones
- Hazard areas

Painless Removal

Easily remove floor markings without damaging the floor or leaving adhesive residue.

- Does not chip and flake when being removed – comes off in one piece
- Clean removal without any unsightly adhesive residue or damage to the floor



B-514 Floor Marking Polyester

ToughStripe® floor marking products are made with Brady's new B-514 polyester. ToughStripe products are ideal for marking aisles, passageways and storage locations, and pointing out important safety equipment and egress paths.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- 2 mil thickness
- Service temperature range of 0°F – 129°F
- Resists harsh chemicals
- Custom colors available



Floor Marking Tape

	Black	White	Red	Green	Blue	Orange	Yellow	Black/Yellow Striped	Red/White Striped	Black/White Striped
2" x 100'	11Z088	11Z095	11Z093	11Z091	11Z090	11Z092	11Z096	11Z089	11Z094	11Z087
3" x 100'	11Z098	11Z106	11Z104	11Z102	11Z101	11Z103	11Z107	11Z099	11Z105	11Z097
4" x 100'	11Z109	11Z116	11Z114	11Z112	11Z111	11Z113	11Z117	11Z110	11Z115	11Z108



Pre-Spaced Shapes

- Quickly lay straight, evenly spaced shapes
- Packaged in rolls (not individually) and spaced 18" apart on a continuous liner
- Easy installation; lay down the continuous tape, and then remove the clear transfer tape. No need to apply markings one by one



Online Video - How to Apply Pre-Spaced Tape

Pre-Spaced Shapes

	Black	White	Red	Green	Blue	Yellow
3.5" x 100' – 55 dots spaced 18" apart	11Z118	11Z121	11Z120	12A025	11Z119	11Z122
2" x 5" x 100' – 52 arrows spaced 18" apart	11Z129	12A027	11Z131	12A026	11Z130	11Z132
2" x 8" x 100' – 46 dashes spaced 18" apart	12D555	12D559	12D558	12D557	12D556	12D560



Dots

	Black	White	Red	Green	Blue	Yellow
3.5" Dia. - 350/roll	11Z123	104405	11Z126	11Z125	11Z124	11Z128



Corner "L" Marks

	Black	White	Red	Green	Blue	Yellow
2" x 5" - 20/pack	11Z157	11Z162	11Z160	11Z159	11Z158	11Z161
3" x 8" - 20/pack	11Z163	12D511	12D510	12D509	12D508	12D512
4" x 10" - 20/pack	12D513	12D517	12D516	12D515	12D514	12D518



Arrows

	Black	White	Red	Green	Blue	Yellow
2" x 5" - 100/pack	11Z133	11Z138	11Z137	11Z134	11Z136	11Z135
3" x 8" - 100/pack	11Z139	11Z143	11Z142	11Z141	11Z140	11Z144
4" x 10" - 100/pack	11Z145	11Z149	11Z148	11Z147	11Z146	11Z150



Center "+" Marks

	Black	White	Red	Green	Blue	Yellow
2" x 5" - 20/pack	12D537	12D541	12D540	12D539	12D538	12D542
3" x 8" - 20/pack	12D543	12D547	12D546	12D545	12D544	12D548
4" x 10" - 20/pack	12D549	12D553	12D552	12D551	12D550	12D554



Foot Prints

	Black	White	Red	Green	Blue	Yellow
10' x 3.5" - 10/pack (5 right & 5 left)	11Z151	11Z155	11Z154	11Z153	11Z152	11Z156



Divider "T" Marks

	Black	White	Red	Green	Blue	Yellow
2" x 5" - 20/pack	12D519	12D523	12D522	12D521	12D520	12D524
3" x 8" - 20/pack	12D525	12D529	12D528	12D527	12D526	12D530
4" x 10" - 20/pack	12D531	12D535	12D534	12D533	12D532	12D536

Custom ToughStripe Tape

- Pre-printed tape with your custom message
- Die cut numbers and letters for safety, lean and other applications
- Specific die cut shape sizes
- Any color you need, just provide a PMS #
- Striped or checkered tape available



Contact your local Grainger sales rep to order your custom ToughStripe® products.



B-483 Print-On-Demand Floor Labels

ToughStripe® floor tape is available in printable label cartridges, which can be used to create custom floor labels. The printable labels feature the same durability and performance as ToughStripe floor marking tape, making them an ideal solution for identifying designated storage locations and providing visual instructions on the shop floor.

Easy 3-step process:

- Print desired label from a select Brady printer
- Position on floor
- Apply included B-634 polyester overlaminates



GlobalMark®2 ToughStripe Floor Marking Tape With Overlaminates

	1.125" x 100'	2.25" x 100'	3" x 100'	4" x 100'
White	12D594	12D602	12A016	12A018
Black	12D589	12D596	-	12A019
Yellow	12D595	12D603	12A017	12A020
Red	12D593	12D601	-	12A021
Blue	12D590	12D597	-	12A022
Green	12D591	12D598	-	12A023
Orange	12D592	12D599	-	12A024

* Specialty black ribbon catalog #96089 required to print on ToughStripe floor tape. Use standard white ribbon catalog #76741 for white text. **Available through sourcing.**



BMP®71 ToughStripe Floor Marking Tape With Overlaminates

	1" x 50'	2" x 50'
White	M71-1000-483-WT-KT	M71-2000-483-WT-KT
Black	M71-1000-483-BK-KT	M71-2000-483-BK-KT
Yellow	M71-1000-483-YL-KT	M71-2000-483-YL-KT
Red	M71-1000-483-RD-KT	M71-2000-483-RD-KT
Blue	M71-1000-483-BL-KT	M71-2000-483-BL-KT
Green	M71-1000-483-GN-KT	M71-2000-483-GN-KT
Orange	M71-1000-483-OR-KT	M71-2000-483-OR-KT

* **All parts available through sourcing.** Specialty black ribbon catalog #M71-R6000 required to print on ToughStripe floor tape. Use standard white ribbon catalog #M71-R4400-WT for white text.



B-534 Floor Marking Signs with Anti-Skid Tread

ToughStripe® floor signs are made with Brady's new B-534 polyester. They are specifically designed to alert workers of potential dangers and enforce protective equipment requirements.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- Service temperature range of 0°F – 129°F
- Resists harsh chemicals
- Black areas of signs are coated with anti-skid tread
- 3 mil thickness
- Circle: 17" diameter
Square: 14" x 18"
- Custom signs available



Arrow Symbol
12D587



Emergency Exit
12D580



Emergency Stairs
12D579



Exit Arrow
12D586



Fire Extinguisher
12D581



Fire Alarm
12D573



Fire Hose
12D585



Pedestrian Traffic Only
12D574



Watch Out For Fork Lift
12D575



Warning Forklift Traffic
12D577



Production Area
12D576



First Aid w/Arrow
12D583



Safety Shower
12D584



Eye Wash
12D578



Stop
12D588



Keep Aisles Clear
12D582



Radiation Area
12D561



First Aid
12D571



Do Not Enter
12D572



Chemical Storage
12D562



Watch Your Step
12D564



No Smoking
12D563



Ear Protection Area
12D568



Eye Protection Area
12D567



Hard Hat Area
12D568



Safety Goggles Required
12D570



Biohazard
12D565



Safety Glasses Required
12D569

Premium 5S Marking Kits

Brady's Premium 5S Marking Kits provide everything you need to 5S your facility, enhancing workplace organization & efficiency.



* Not all Kit contents shown.
IDXPERT™ Printer not included in all kits.

Premium 5S Marking Kit includes:

- ToughStripe® Floor Marking Tape
 - 4 Rolls of 2" ToughStripe floor tape (1 yellow, 1 red, 1 blue, 1 green)
 - 4 Packages of 2" L-shaped corner marks (1 yellow, 1 red, 1 blue, 1 green)
- Toolboard / Workbench Marking Tapes
 - 4 Rolls of 12" shadow vinyl (1 black, 1 red, 1 blue, 1 green)
 - 4 Rolls of 1/2" border tape (1 black, 1 red, 1 blue, 1 green)
 - 4 Rolls of 1/2" L-shaped corner marks (1 black, 1 red, 1 blue, 1 green)

Premium 5S Marking Kit with IDXPERT™ Printer includes:

- All contents of Premium 5S Marking Kit above
- IDXPERT™ Continuous Only Label Printer with AC adaptor
- 3 Black on white tape cartridges (1/2", 1", 1 1/2")
- 1 Black on yellow tape cartridge (1 1/2")
- 1 Red on white tape cartridge (1 1/2")

Premium 5S Kit with BMP®71 Label Printer includes:

- All contents of Premium 5S Marking Kit above
- BMP®71 Printer with hard carrying case and charger/AC power adaptor
- 3 White vinyl tape cartridges (1/2", 1", 2")
- 1 Yellow vinyl tape cartridge (2")
- 2 Ribbon cartridges (1 black, 1 red)

Catalog #	Description
142109	Premium 5S Kit
142110	Premium 5S Kit with IDXPERT Printer
142111	Premium 5S Kit with BMP71 Label Printer

* All parts available through sourcing.



For more information contact your local Grainger sales representative or visit: [Grainger®.com](http://Grainger.com)

AVAILABLE THROUGH

GRAINGER®
FOR THE ONES WHO GET IT DONE