Square Back Mini Cartridge Systems

COX dispensers are innovatively designed and manufactured under rigid quality control. Applicators for mini cartridge systems are available in manual and pneumatic variants configured for 1:1, 2:1, 4:1 and 10:1 mix ratios. All applicators are lightweight, compact and durable, offering ergonomically efficient dispensing for a long trouble-free service with low cost of ownership.



M25

- 25 ml. x 25 ml.
- Dedicated 1:1 Mix Ratio
- Mechanical Advantage 11:1
- · Easy Loading Breech Secure Fit
- Full Cartridge Support





- · 25 ml. x 25 ml.
- Dedicated 1:1 Mix Ratio
- Available in 2:1 Mix Ratio for a 37.5 ml. System Model A25/2
- · Nominal Thrust 235 lbs.
- · Easy Loading Breech
- True Adjustable Air Regulator 75 PSI Maximum Output
- 145 PSI Maximum Input
- · Silencer & Instant Dump Valve



MP25



- Mix Ratios (Must Specify)
- True Adjustable Air Regulator -50 PSI Maximum Output
- 145 PSI Maximum Input
- · Silencer & Instant Dump Valve





Quality Sealant Applicators

(800) 822-8114 www.cox-applicators.com sales@cox-applicators.com



- MR50 Series
- Square Back Cartridges MR25 Series
- Round & Square Back Cartridges (full kit) Model MR50/25
- 25 ml. 1:1 Plunger Rack for Round Back Also Available
- 37.5 ml. 2:1 Plunger Rack for Square Back Also Available
- 50 ml. 4:1 and 10:1 Extended Length Plunger Racks for Square Back Also Available
- 75 ml. 1:1 Plunger Rack for Square and Round Back Also Available
- · Lightweight Molded From Glass Reinforced ABS
- · Easy Loading Breech Secure Fit

Private Label and Custom Color Options Available







