




The 7000 Series is now available in a **Complete One-Box Solution**

7000 Series

The dual pre-load solution for cylindrical latch bolts and rim exit devices

Offers two solutions to address pre-loaded doors. The in-frame adjustable feature allows the installer to easily adjust the electric strike opening to accommodate the horizontal position of the latchbolt after installation. The pre-load release function allows the electric strike to operate smoothly throughout the year under varying loads on the door caused by air-conditioning pressure, changes in the weather, warped doors or doors with weather stripping that often bind standard electric strikes. This unit accommodates cylindrical latchbolts up to 5/8" throw and rim exit latchbolts up to 3/4" throw.



Specifications

- UL 1034, burglary-resistant listed
- ANSI BHMA A156.31, Grade 1 (791 and 792 options)
- ANSI/BHMA A156.31, Grade 2 (783S, 786S, and 789S options)
- MEA New York City accepted
- Patents: #5,484,180

Frame Application

- Metal
- Wood

Electrical

- .45 Amps @ 12VDC continuous duty
- .25 Amps @ 24VDC continuous duty

7000 Models


7000

Universal electric strike
Faceplate options ordered separately, see page 30


NEW!

7000C

Complete electric strike
Includes the 791 and 792 faceplates in the box



Model 7000C includes a 791 and a 792 faceplate in the box



Standard Features

- Stainless steel construction
- Tamper resistant
- Static strength 1,500 lbs. (791 and 792 options)
- Dynamic strength 70 ft.-lbs. (791 and 792 options)
- Static strength 1,000 lbs. (783S, 786S, and 789S options)
- Dynamic strength 50 ft.-lbs. (783S, 786S, and 789S options)
- Endurance 500,000 cycles
- Field selectable fail secure/ fail safe
- Accommodates pre-load (fail secure only)
- Horizontal adjustment
- Non-handed
- Internally mounted solenoid
- Strike body depth 1-11/16"
- Plug-in connector
- Trim enhancer (791 and 792 options)
- Pocket adapter (786S and 789S options)
- Three-year limited warranty

Optional Features

- **LBM** - Latchbolt monitor

Accessories

- SMB** - Surface mounting box (783S and 789S options)
- 7000-104** - Lip extension trim adapter
- 7000-105** - Trim enhancer (goof plate)
- 7000-106** - Keeper pocket adapter
- 7000-107** - Full keeper shim pack
- 7000-108** - 1/8" spacer plate (783S and 789S options, black finish only)
- 7000-110** - Replacement strike plate (791 and 792 option)
- 150** - Strike latch guard
- 154-MTK** - Metal template kit
- 2001M** - Plug-in bridge rectifier
- 2004M** - ElectroLynx® adapter
- 2005M3** - SMART Pac III™
- 2006M** - Plug-in buzzer

Finishes

(791 and 792 options)

- 630** - Satin stainless steel
- 605** - Bright brass
- 606** - Satin brass
- 612** - Satin bronze
- 613C** - Brown nylon powder coated
- 629** - Bright stainless steel
- BLK** - Black

Finishes

(783S, 786S and 789S options)

- 613C** - Brown nylon powder coated
- 626** - Brushed chrome



CYLINDRICAL LOCKSETS



RIM EXIT DEVICES



UL 1034
BURGLARY LISTED









FIELD SELECTABLE
(FAIL SECURE / FAIL SAFE)

hes
ASSA ABLOY

7000 Series Faceplate Options












Operation: After releasing the latchbolt, the keeper returns to the locked position.

 <p>4-7/8" x 1-1/4"</p>	<p>791 Option For use with: Cylindrical locksets up to 5/8" throw. » ANSI/BHMA Numbers: #E09321, #E09322, #E09323</p>	  <p>GRADE 1</p>
 <p>7-15/16" x 1-7/16"</p>	<p>792 Option For use with: Cylindrical locksets up to 5/8" throw. » ANSI/BHMA Numbers: #E09321, #E09322, #E09323</p>	  <p>GRADE 1</p>



Operation: After releasing pullman latch, the keeper returns to the locked position.

 <p>9" x 1-3/4" x 11/16"</p>	<p>783S Option For use with: Rim exit devices in metal jambs with up to a 3/4" pullman latch. Compatible locksets: American Device, Arrow, Dor-O-Matic, Monarch, Precision, Sargent, Von Duprin, Yale » ANSI/BHMA Numbers: #E09311, #E09312, #E09313</p>	  <p>GRADE 2</p>
 <p>6-1/2" x 1-3/4" x 1/2"</p>	<p>786S Option For use with: Rim exit devices in aluminum jambs and surface mounted vertical rod exit devices with up to a 3/4" pullman latch. Compatible locksets: American Device, Arrow, Dor-O-Matic, Jackson, Monarch, Precision, Sargent, Von Duprin, Yale » ANSI/BHMA Numbers: #E09311, #E09312, #E09313</p>	  <p>GRADE 2</p>
 <p>9" x 1-3/4" x 1/2"</p>	<p>789S Option For use with: Rim exit devices in aluminum jambs with up to a 3/4" pullman latch. Includes keeper pocket adapter. Compatible locksets: American Device, Arrow, Dor-O-Matic, Jackson, Monarch, Precision, Sargent, Von Duprin, Yale » ANSI/BHMA Numbers: #E09311, #E09312, #E09313</p>	  <p>GRADE 2</p>