

305 Stainless Steel Beam Clamp, Top Mount

3050050S4



Features

- Pressed steel beam clamp
- Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI/MSS-SP-58 (Type 19 and 23), install in accordance with ANSI/MSS-SP-69
- Structural attachment to top flange of metal beams, purlins, channel, or angle iron

Product Specifications

Part Number	3050050S4
Material	Stainless steel 304
Rod Size (RS)	1/2"
Flange Thickness (FT)	5/8" Max
A	7/8"
Screw Diameter (Sc)	3/8"
Screw Length (L)	1 1/2"
Torque (TQ)	5 ft lb
Static Load (F)	1,130 lb
Standard Packaging Quantity	100 pc
UPC	78285659688
UNSPSC	31162905

Set screw must be tightened and torqued onto the sloped side of the I-beam, channel, or angle iron flange.

Recognizing that torque wrenches are generally not used or available on many job sites, the setscrew should be tightened so it contacts the I-beam and then an additional 1/4 to 1/2 turn added.

