

# NEW



# M18 FUEL™

DRIVEN TO OUTPERFORM.™



**MOST  
POWERFUL**

**MOST  
COMPACT**

**AUTOSTOP™**  
CONTROL MODE,  
ENHANCED SAFETY

**M18 FUEL™ 2-Tool Combo Kit:  
1/2" Hammer Drill/Driver and  
1/4" Hex Impact Driver**

3697-22 / 794JL0


**REDLITHIUM™**  
**XC5.0**



# DRIVEN TO OUTPERFORM.™

M18 FUEL™ is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL™ products feature three MILWAUKEE® exclusive innovations — the POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software — that deliver unmatched power, run-time and durability. Simply put, the M18 FUEL™ 1/2" Hammer Drill/Driver and the M18 FUEL™ 1/4" Hex Impact Driver are the industry's best high performance drill and impact driver.

## M18 FUEL™



### 2 REDLINK PLUS™ INTELLIGENCE

- Most Advanced Electronic System on the Market for Maximum Performance
- Total System Communication with Overload Protection Increases Tool Life



### 3 REDLITHIUM™ XC5.0 BATTERY PACK

- Most Durable Pack on the Market
- Over 2X More Recharges than Leading Competitor
- Fuel Gauge Displays Remaining Charge
- Operates Below -18°C / 0°F


### 1 POWERSTATE™ BRUSHLESS MOTOR

- MILWAUKEE® Designed and Built Brushless Motor
- Outperforms All Leading Competitors



## MOST POWERFUL DRILL


MAINTAINS HIGHEST POWER UNDER LOAD



■ MILWAUKEE® ■ Competitor 1 ■ Competitor 2

## FASTEST DRIVING IMPACT


UP TO 30% FASTER



■ MILWAUKEE® ■ Fastest Competitor

## AUTOSTOP™ CONTROL MODE, ENHANCED SAFETY

PREVENTS OVER ROTATION



■ MILWAUKEE® ■ Competitor

## 2-TOOL COMBO KIT

# M18 FUEL™

### UPGRADED FAN

Increased air flow to deliver 60% cooler operation for ability to drill more holes back-to-back

### POWERSTATE™ BRUSHLESS MOTOR

All-new motor design and innovative motor control for faster app speed and the most powerful drill in the industry

### ALL-METAL CHUCK

Improved bit retention and increased durability

### TWO SPEED CONTROL

Adjust drill speed for increased performance and control

### NEW MECHANICAL CLUTCH

New M-clutch design for wider range of torque settings and improved fastening performance

### AUTOSTOP™ MODE LIGHT

Dedicated light to indicate when AUTOSTOP™ protection events occur

### POWERSTATE™ BRUSHLESS MOTOR

Delivers unmatched power and speed for a full range of capability to complete the widest variety of applications

### TRI-LED WORKLIGHTS

Maximum workspace visibility

### PREMIUM RUBBER OVERMOLD

Increased comfort for all-day use

### 4-MODE DRIVE CONTROL™

Provides greater control over output speed and power

### ULTIMATE TRIGGER CONTROL

Smooth acceleration for small fasteners to prevent stripping of screws or damaging of materials



## SPECIFICATIONS AND MODELS

DESCRIPTION	2904 SPECIFICATIONS
Chuck Type	1/2" All-Metal Chuck
Peak Torque	1,400 in-lbs
No Load RPM	0 – 500 / 0 – 2,100
BPM	33,000
Length	6.9"

DESCRIPTION	2953 SPECIFICATIONS
Chuck Type	1/4" Hex
Max Torque	2,000 in-lbs
RPM	0 – 3,900
IPM	0 – 4,400
DRIVE CONTROL™	4-Mode
Single Handed Bit Insertion	Yes
Tri-LED	Yes
Length	4.47"



### M18 FUEL™ 2-Tool Combo Kit 3697-22 / 794JLO

Includes: 2904-20 1/2" Hammer Drill/Driver, 2953-20 1/4" Hex Impact Driver, (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, M18™ & M12™ Multi-Voltage Charger, Side Handle, (2) Belt Clips and Carrying Case.





**M18**™

**PERFORMANCE DRIVEN  
TRADE FOCUSED  
SYSTEM WIDE**



M18 FUEL™ 2-Tool Combo Kit  
M722-5648

[milwaukeetool.com](http://milwaukeetool.com)

©2022 Milwaukee® Tool

[GRAINGER.COM](http://GRAINGER.COM)® | 1.800.GRAINGER

AVAILABLE THROUGH  
**GRAINGER**®  
FOR THE ONES WHO GET IT DONE