


CUSTOMER SPECIFICATION DRAWING



CLAMP PART NUMBER	MATERIAL		INSIDE DIA.	WIDTH ±.005	MATERIAL THICKNESS ±.0015	TAIL LENGTH	LIP LGTH. +.125 -.062	BUCKLE HEIGHT MAX.	QTY	WEIGHT PER BOX (LBS.)	
	BAND	BUCKLE									A
GRP03S	201L SS	201SS	.813	.375	.025	3.44	.750	.163	10	.458	
GRP311S			1.375						10	.545	
GRP04S			1.000	.625					3.50	10	.791
GRP05S			1.250							10	.828
GRP06S			1.500							10	.940
GRP07S			1.750							10	1.005
GRP08S			2.000			10				1.138	
GRP09S			2.250			10				1.207	
GRP10S			2.500			10			1.278		
GRP11S			2.750			10			1.331		
GRP12S			3.000	10		1.404					
GRP16S			4.000	10		1.689					

NOTES:



1. BAND AND BUCKLE MATERIAL PER BAND-IT SPECIFICATION.

ABOVE SPECIFICATION CERTIFIED BY: _____ DATE: _____

TITLE: _____

UNLESS OTHERWISE NOTED:
DIMENSIONS ARE IN INCHES
AFTER FINISH

TOLERANCES:

X ±0.100
.XX ±0.020
.XXX ±0.005
.XXXX ±0.001
ANGLES ±0.5°

BAND-IT®

A unit of ~~IDEX~~ Corporation
P.O. Box 16307
Denver, Colorado U.S.A.

PROPRIETARY AND CONFIDENTIAL

THIS DRAWING WITH ALL CONTENTS IS PROPERTY OF BAND-IT-IDEX, INC. REPRODUCTION, DISCLOSURE OR MFG. OF MATTER SHOWN IS PROHIBITED WITHOUT WRITTEN PERMISSION. DO NOT SCALE DRAWING

TITLE:

**CENTER PUNCH
CLAMPS, GRAINGER**

DWG. NO.

GRP200

REV -

SHEET 3 OF 3