

24" Double Blade Ultra Hygiene Squeegee Series 7714





Blades are replaceable (part 7734) to extend the overall life of the squeegee

This floor squeegee is used for drying surfaces after a sanitizing process. The double-blade nonporous rubber design of this squeegee is effective in removing water from all types of floors, such as tiles, epoxy, and cement. The cartridge system blades can be removed for easy cleaning and replaced when worn out, making the model a very economical hygienic option. Replacement Squeegee Blade: Series 7734.



24" Double Blade Ultra Hygiene Squeegee 7714

1 2 3 4 5 6 7 8 9

The double rubber blades move water and debris more efficiently than a single-blade squeegee. The cartridge is replaceable to make the head more cost-effective. The hygienic design means fewer places for microorganisms to hide and multiply.

Specifications:

Length: 23.6" Width: 3.7" Height: 4.3" FDA-Compliant Raw Material: Yes Material: Polypropylene/Rubber Unit Weight: 0.84 lbs. Replacement Squeegee Blade: 7734

Colors

When ordering, add the color digit to the base part number to denote color.



Fully updated product specifications are available at Vikan.com.

The Color-Coding System

Remco and Vikan[®] brands offer an integrated color-coding system to help mitigate the risk of cross-contamination in food processing facilities. With an array of color-coded tools and



storage brackets, and years of experience building effective color-coding systems, the experts at Remco Products Corporation can help you effectively apply color-coding to divide and identify different zones or processing tasks. As a result, workers can more easily comply with material handling and hygienic cleaning procedures to maintain stringent food safety standards.



Please see the full-line catalog for a complete list of Remco[™] and Vikan[®] products.







Scrapers



Tubs



'ika∩

Remco Products Corporation

4735 West 106th Street Zionsville, Indiana 46077

PHONE: 317.876.9856 | FAX: 800.585.8619

www.remcoproducts.com