


CUSTOMER SPECIFICATION DRAWING



CLAMP PART NUMBER	MATERIAL		INSIDE DIA.	WIDTH ±.005	MATERIAL THICKNESS ±.0015	TAIL LENGTH	LIP LGTH. +.125 -.062	BUCKLE HEIGHT MAX.	QTY	WEIGHT PER BOX (LBS.)	
	BAND	BUCKLE	A	B	C	D	E	F			
GRP039	G.C.S.	201SS	.813	.375	.025	3.44	.750	.163	10	.466	
GRP311			1.375						10	.559	
GRP049		201/301SS	1.000	.625					3.50	10	.818
GRP059			1.250							10	.852
GRP069			1.500							10	.968
GRP079			1.750							10	1.035
GRP089			2.000			10				1.172	
GRP099			2.250			10				1.243	
GRP109			2.500			10			1.316		
GRP119			2.750			10			1.371		
GRP129		3.000	10	1.446							
GRP169		4.000	10	1.740							

NOTES:

1. BAND AND BUCKLE MATERIAL PER BAND-IT SPECIFICATION.

ABOVE SPECIFICATION CERTIFIED BY: _____ DATE: _____

TITLE: _____

UNLESS OTHERWISE NOTED:
DIMENSIONS ARE IN INCHES
AFTER FINISH

TOLERANCES:
.X ±0.100
.XX ±0.020
.XXX ±0.005
.XXXX ±0.001
ANGLES ±0.5°

BAND-IT®

A unit of ~~IDEX~~ Corporation
P.O. Box 16307
Denver, Colorado U.S.A.

PROPRIETARY AND CONFIDENTIAL

THIS DRAWING WITH ALL CONTENTS IS PROPERTY OF BAND-IT-IDEX, INC. REPRODUCTION, DISCLOSURE OR MFG. OF MATTER SHOWN IS PROHIBITED WITHOUT WRITTEN PERMISSION. DO NOT SCALE DRAWING

TITLE:

**CENTER PUNCH
CLAMPS, GRAINGER**

DWG. NO.

GRP200

REV -

SHEET 2 OF 3