

ADDISON™ PROTECTIVE EYEWEAR

CHOOSE FROM SCRATCH-RESISTANT OR ANTIFOG LENS COATINGS



BECAUSE YOU TAKE **SAFETY** PERSONALLY™



KEY PRODUCT ATTRIBUTES

- Economical eye protection
- Meets or exceeds ANSI Z87.1-2010 safety standards
- Polycarbonate, one-piece molded frame and lens
- Wraparound lens construction with two focal points
- Provides 99.9% UV protection
- Comfortable, soft rubber nosepiece
- Frame width: 5³/₈" between hinge points
- Bayonet temples with rubber (TPR) grips for enhanced comfort

Model Number	Lens Color	Lens Coating	Frame Color	Visible Light Transmission (VLT) Range (%)
4VCK9	Clear	Scratch Resistant	Clear	Over 90%
4VCL2	Clear	Antifog	Clear	Over 90%
4VCL1	Gray	Scratch Resistant	Gray	13% ± 3%
4VCL4	Gray	Antifog	Gray	13% ± 3%
4VCL3	Indoor/Outdoor	Scratch Resistant	Gray	50 ± 5%
4VCL5	Amber	Scratch Resistant	Amber	88% ± 3%
4VCL6	Blue Mirror	Scratch Resistant	Gray	15 ± 5%
4VCL7	Red Mirror	Scratch Resistant	Gray	12 ± 5%