

V EYEWEAR

AVAILABLE IN SCRATCH-RESISTANT, UNCOATED & ANTIFOG LENS COATINGS



BECAUSE YOU TAKE **SAFETY** PERSONALLYSM

KEY PRODUCT ATTRIBUTES

- Economical
- Meets ANSI Z87.1-2010
- Provides 99.9% UV protection
- One-piece molded, polycarbonate frame and lens
- Spatula-style, polycarbonate frosted temples
- Polycarbonate nosepiece integrated into the lens
- Wraparound lens construction with two focal points
- Overall temple width:
5-9/16"W ± 1/8"W
- Temple width (distance measured between center hinge points):
5-1/4"W ± 1/16"W
- Overall lens dimension (± 1/16"):
3-1/16"L ± 1-23/32"W



4VCF8



4VCG1



1FYX6



1FYX8



1XPJ5



1XPK6

Model Number	Lens Color	Lens Coating	Frame Color	Visible Light Transmission (VLT) Range (%)
4EY97	Clear	Uncoated	Frosted Clear	Over 90%
1FYX6	Clear	Scratch Resistant	Frosted Clear	Over 90%
1FYX7	Clear	Antifog	Frosted Clear	Over 90%
1FYX8	Gray	Scratch Resistant	Frosted Gray	13 ± 3%
1XPJ5	Amber	Scratch Resistant	Frosted Amber	88 ± 3%
1XPK6	Light Blue	Scratch Resistant	Frosted Blue	71 ± 3%
1XPR2	Indoor/Outdoor	Scratch Resistant	Frosted Clear	50 ± 5%
2ERE6	Silver Mirror	Scratch Resistant	Frosted Gray	15 ± 5%
4VCF8	Blue Mirror	Scratch Resistant	Gray	25 ± 5%
4VCF9	Rainbow Mirror	Scratch Resistant	Gray	13 ± 5%
4VCG1	Red Mirror	Scratch Resistant	Gray	30 ± 5%
4VCG2	Gray	Antifog	Gray	13 ± 3%