

XtremeFLEX® BWH-D Dual Element Heating Tapes


Product Highlights

- ✓ Dual heater element design increases flexibility
- ✓ Connects easily to your choice of temperature control
- ✓ Includes high-temperature tie-downs for easy installation



Specifications:

- Highly flexible and durable multi-stranded dual heating element provides even heat across tape
- Reinforced with high temperature Samox® fiberglass for added strength and durability
- Maximum exposure temperature: 1400°F (760°C)
- Power density: 13.1 watts/in² (0.020 watts/mm²)
- Suitable for electrical conductive surfaces
- 24" (610mm) power leads with
 - 120VAC: standard 2-prong (NEMA 1-15) plug
 - 240VAC: bare-wire connection



Ordering Information:

Width in (mm)	Length ft (m)	Total Watts	Part No. 120VAC	Part No. 240VAC
0.5 (13)	2 (0.6)	156	BWH051020LD	BWH052020LD*
0.5 (13)	4 (1.2)	312	BWH051040LD	BWH052040LD*
0.5 (13)	6 (1.8)	468	BWH051060LD	BWH052060LD*
0.5 (13)	8 (2.4)	624	BWH051080LD	BWH052080LD*
0.5 (13)	10 (3.1)	780	BWH051100LD	BWH052100LD*
1.0 (25)	2 (0.6)	312	BWH101020LD	BWH102020LD*
1.0 (25)	4 (1.2)	624	BWH101040LD	BWH102040LD*
1.0 (25)	6 (1.8)	936	BWH101060LD	BWH102060LD*
1.0 (25)	8 (2.4)	1248	BWH101080LD	BWH102080LD*

* Plug not included

NEW



AVAILABLE THROUGH

GRAINGER®

FOR THE ONES WHO GET IT DONE



Short Video: How to Easily Select and Install Heating Tapes

HEATING TAPES

IMPORTANT: Temperature controller is required for this product. Please contact us for more information.